

## 600µm 0.22 NA UV/VIS Fiber, 10m Length



Stock #57-070 CLEARANCE **3 In Stock**

⊖ 1 ⊕ £259<sup>16</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	£259.16 each
Need More?	<a href="#">Request Quote</a>

**i** Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

**Note:**

Fiber ends are not polished.

### Physical & Mechanical Properties

660 ±13.2 **Cladding Diameter (µm):**

132/66 (Continuous/Momentary) **Minimum Bend Radius (mm):**

10.00	Length (m):
710 ±15	Outer Diameter (µm):
600 ±12	Core Diameter (µm):
<b>Optical Properties</b>	
25.4	Acceptance Angle (°):
UVMS	Coating:
Fused Silica	Substrate: <input type="checkbox"/>
0.22	Numerical Aperture NA:
1.457	Index of Refraction (n <sub>d</sub> ) - Core:
1.439	Index of Refraction (n <sub>d</sub> ) - Cladding:
190 - 1250	Wavelength Range (nm):
±0.02	Numerical Aperture (NA) Tolerance:
<b>Material Properties</b>	
Polyimide	Buffer Material:
<b>Environmental &amp; Durability Factors</b>	
-190 to +390	Operating Temperature (°C):
<b>Regulatory Compliance</b>	
<a href="#">Compliant</a>	RoHS 2015:
<a href="#">Compliant</a>	Reach 209:
<a href="#">View</a>	Certificate of Conformance:

## Product Details

### UV/VIS Optical Fibers

- High OH Content
- Fused Silica Core
- Stepped Index
- Multimode Fiber

### VIS/NIR Optical Fibers

- Low OH Content
- Ideal for Use with NIR Diode Lasers
- Fused Silica Core
- Stepped Multimode Fiber

Buffered Fiber Optics are ideal for regions of the UV/Visible and Visible/NIR spectrum not covered by our plastic optical fibers. These fibers have a fused silica core and cladding, as well as a polymer buffer for added protection. Fiber diameters of 50µm – 600µm feature a high temperature, high strength polyimide buffer, while the 1mm fibers are buffered with nylon for greater protection. Buffered Fiber Optics are offered in UV/MS or VIS/NIR Fibers in 10 and 25m lengths, from 50 to 600µm.

**Note:** Fiber ends are not polished.

## Technical Information

