

TECHSPEC® 6.0mm Dia. x 36.0mm FL, MgF₂ Coated, Plano-Convex Lens



Stock **#32-849** 3-4 DAYS

[Other Coating Options](#)

- 1 + **£27.20**

ADD TO CART

Qty 1-9
£27.20
Qty 10+
£24.44
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
6.00 +0.0/-0.025

Effective Focal Length EFL (mm):

36.00 @ 587.6nm
Back Focal Length BFL (mm): 34.95
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤ 1.75% @ 400 - 700nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 1.60 ± 0.05
Edge Thickness ET (mm): 1.36
Radius R₁ (mm): 18.61
Clear Aperture CA (mm): 5.4
f/#: 6
Numerical Aperture NA: 0.08
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 400 - 700
Damage Threshold, By Design: ☐ 10 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant