

[See all 423 Products in Family](#)

TECHSPEC[®] 6.0mm Dia. x 36.0mm FL, NIR I Coated, Plano-Convex Lens



Stock **#48-722** **5 In Stock**

☐ [Other Coating Options](#)

-

1

+

£34^{.00}

ADD TO CART

Volume Pricing	
Qty 1-9	£34.00 each
Qty 10-24	£30.40 each
Qty 25-49	£27.20 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Plano-Convex Lens

Type:

Physical & Mechanical Properties

6.00 +0.0/-0.025	Diameter (mm):
<1	Centering (arcmin):
1.60 ±0.05	Center Thickness CT (mm):
1.36	Edge Thickness ET (mm):
5.4	Clear Aperture CA (mm):
Protective as needed	Bevel:
Optical Properties	
36.00 @ 587.6nm	Effective Focal Length EFL (mm):
34.95	Back Focal Length BFL (mm):
NIR I (600-1050nm)	Coating:
R _{avg} ≤0.5% @ 600 - 1050nm	Coating Specification:
N-BK7	Substrate: □
40-20	Surface Quality:
1.5λ	Power (P-V) @ 632.8nm:
λ/4	Irregularity (P-V) @ 632.8nm:
±1	Focal Length Tolerance (%):
18.61	Radius R ₁ (mm):
6	f/#:
0.08	Numerical Aperture NA:
600 - 1050	Wavelength Range (nm):
7 J/cm ² @ 1064nm, 10ns	Damage Threshold, By Design: □

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume


Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details






- AR Coated to Provide <0.5% Reflectance per Surface for 600 - 1050nm
- Designed for 0° Angle of Incidence
- Various PCX Coating Options: [Uncoated](#), [MgF₂](#), [VIS 0°](#), [VIS-NIR](#), [NIR II](#), [VIS-EXT](#), and [YAG-BBAR](#)

TECHSPEC® NIR I Coated Plano-Convex (PCX) Lenses have a positive focal length, making them ideal for collecting and focusing light in imaging applications. They are also useful in a variety of applications involving emitters, detectors, lasers, and fiber optics. TECHSPEC® NIR I Coated Plano-Convex (PCX) Lenses are available in a wide variety of diameters and focal lengths. Identical designs of these PCX lenses are also offered [uncoated](#) or with broadband anti-reflective (BBAR) coatings, which include [MgF₂](#), [VIS 0°](#), [VIS-NIR](#), [NIR II](#), [VIS-EXT](#), and [YAG-BBAR](#).

Technical Information



N-BK7																													
Uncoated N-BK7 Typical Transmission <table border="1"><caption>Uncoated N-BK7 Typical Transmission Data (Approximate)</caption><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>200</td><td>70</td></tr><tr><td>300</td><td>85</td></tr><tr><td>400</td><td>92</td></tr><tr><td>600</td><td>93</td></tr><tr><td>800</td><td>93</td></tr><tr><td>1000</td><td>93</td></tr><tr><td>1200</td><td>93</td></tr><tr><td>1400</td><td>93</td></tr><tr><td>1600</td><td>93</td></tr><tr><td>1800</td><td>92</td></tr><tr><td>2000</td><td>91</td></tr><tr><td>2200</td><td>89</td></tr></tbody></table>	Wavelength (nm)	Transmission T (%)	200	70	300	85	400	92	600	93	800	93	1000	93	1200	93	1400	93	1600	93	1800	92	2000	91	2200	89	Typical transmission of a 3mm thick, uncoated N-BK7 window across the UV - NIR spectra. Click Here to Download Data		
Wavelength (nm)	Transmission T (%)																												
200	70																												
300	85																												
400	92																												
600	93																												
800	93																												
1000	93																												
1200	93																												
1400	93																												
1600	93																												
1800	92																												
2000	91																												
2200	89																												
N-BK7 with MgF₂ Coating Typical Transmission <table border="1"><caption>N-BK7 with MgF₂ Coating Typical Transmission Data (Approximate)</caption><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>200</td><td>70</td></tr><tr><td>300</td><td>85</td></tr><tr><td>400</td><td>95</td></tr><tr><td>500</td><td>98</td></tr><tr><td>600</td><td>97</td></tr><tr><td>800</td><td>95</td></tr><tr><td>1000</td><td>94</td></tr><tr><td>1200</td><td>93</td></tr><tr><td>1400</td><td>93</td></tr><tr><td>1600</td><td>93</td></tr><tr><td>1800</td><td>92</td></tr><tr><td>2000</td><td>91</td></tr><tr><td>2200</td><td>90</td></tr></tbody></table>	Wavelength (nm)	Transmission T (%)	200	70	300	85	400	95	500	98	600	97	800	95	1000	94	1200	93	1400	93	1600	93	1800	92	2000	91	2200	90	Typical transmission of a 3mm thick N-BK7 window with MgF₂ (400-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 1.75\% @ 400 - 700\text{nm}$ (N-BK7) Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Wavelength (nm)	Transmission T (%)																												
200	70																												
300	85																												
400	95																												
500	98																												
600	97																												
800	95																												
1000	94																												
1200	93																												
1400	93																												
1600	93																												
1800	92																												
2000	91																												
2200	90																												
N-BK7 with VIS-EXT Coating Typical Transmission <table border="1"><caption>N-BK7 with VIS-EXT Coating Typical Transmission Data (Approximate)</caption><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>200</td><td>70</td></tr><tr><td>300</td><td>85</td></tr><tr><td>350</td><td>95</td></tr><tr><td>400</td><td>98</td></tr><tr><td>500</td><td>99</td></tr><tr><td>600</td><td>99</td></tr><tr><td>700</td><td>99</td></tr><tr><td>800</td><td>95</td></tr><tr><td>900</td><td>88</td></tr><tr><td>1000</td><td>82</td></tr><tr><td>1100</td><td>78</td></tr><tr><td>1200</td><td>78</td></tr></tbody></table>	Wavelength (nm)	Transmission T (%)	200	70	300	85	350	95	400	98	500	99	600	99	700	99	800	95	900	88	1000	82	1100	78	1200	78	Typical transmission of a 3mm thick N-BK7 window with VIS-EXT (350-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.5\% @ 350 - 700\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data		
Wavelength (nm)	Transmission T (%)																												
200	70																												
300	85																												
350	95																												
400	98																												
500	99																												
600	99																												
700	99																												
800	95																												
900	88																												
1000	82																												
1100	78																												
1200	78																												
N-BK7 with VIS-NIR Coating Typical Transmission <table border="1"><caption>N-BK7 with VIS-NIR Coating Typical Transmission Data (Approximate)</caption><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>200</td><td>75</td></tr><tr><td>300</td><td>85</td></tr><tr><td>400</td><td>98</td></tr><tr><td>500</td><td>96</td></tr><tr><td>600</td><td>98</td></tr><tr><td>700</td><td>98</td></tr><tr><td>800</td><td>98</td></tr><tr><td>870</td><td>98</td></tr><tr><td>900</td><td>95</td></tr><tr><td>1000</td><td>88</td></tr><tr><td>1100</td><td>80</td></tr><tr><td>1200</td><td>75</td></tr></tbody></table>	Wavelength (nm)	Transmission T (%)	200	75	300	85	400	98	500	96	600	98	700	98	800	98	870	98	900	95	1000	88	1100	80	1200	75	Typical transmission of a 3mm thick N-BK7 window with VIS-NIR (400-1000nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 0.25\% @ 880\text{nm}$ $R_{avg} \leq 1.25\% @ 400 - 870\text{nm}$ $R_{avg} \leq 1.25\% @ 890 - 1000\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data		
Wavelength (nm)	Transmission T (%)																												
200	75																												
300	85																												
400	98																												
500	96																												
600	98																												
700	98																												
800	98																												
870	98																												
900	95																												
1000	88																												
1100	80																												
1200	75																												

	Click Here to Download Data
N-BK7 with VIS 0° Coating Typical Transmission 	Typical transmission of a 3mm thick N-BK7 window with VIS 0° (425-675nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.4\%$ @ 425 - 675nm Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
N-BK7 with YAG-BBAR Coating Typical Transmission 	Typical transmission of a 3mm thick N-BK7 window with YAG-BBAR (500-1100nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 0.25\%$ @ 532nm $R_{abs} \leq 0.25\%$ @ 1064nm $R_{avg} \leq 1.0\%$ @ 500 - 1100nm Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
N-BK7 with NIR I Coating Typical Transmission 	Typical transmission of a 3mm thick N-BK7 window with NIR I (600 - 1050nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.5\%$ @ 600 - 1050nm Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
N-BK7 with NIR II Coating Typical Transmission 	Typical transmission of a 3mm thick N-BK7 window with NIR II (750 - 1550nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 1.5\%$ @ 750 - 800nm $R_{abs} \leq 1.0\%$ @ 800 - 1550nm $R_{avg} \leq 0.7\%$ @ 750 - 1550nm Data outside this range is not guaranteed and is for reference only. Click Here to Download Data

Compatible Mounts

;