


5mm Diameter Laser Diode Mirror



Stock **#46-617** 10 In Stock

-

1

+

£22⁴⁰

ADD TO CART

Volume Pricing	
Qty 1-10	£22.40 each
Qty 11-24	£17.60 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Type:

Flat Mirror

Physical & Mechanical Properties

5.00 ±0.25	Diameter (mm):
±0.25	Dimensional Tolerance (mm):
3.00	Thickness (mm):
Optical Properties	
Float Glass	Substrate: □
80-50	Surface Quality:
R _{abs} >97% @ 633nm	Coating Specification:
Dielectric Mirror (500-700nm)	Coating:
Dielectric	Coating Type:
633	Design Wavelength DWL (nm):
Environmental & Durability Factors	
ML-C-48497A	Durability:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

PRODUCT DETAILS

• Over 95% Reflectance of Visible Laser Diode Light


• Ideal for Multiple Reflection Systems

• Coating Optimized for 633nm at 45° AOI

Visible Laser Diode Mirrors are specially coated to attain maximum reflection of visible laser diodes. Optimized for 633nm at a 45° angle of incidence, these mirrors provide 97% reflectance versus only 85 - 90% for standard first surface mirrors. This reduced loss is particularly important in multiple reflection systems, where loss can significantly impact system efficiency. Visible Laser Diode Mirrors feature a float glass substrate and are ideal for multiple reflection systems.

TECHNICAL INFORMATION

Visible Laser Diode Mirror Reflectance at 45°



@ 500nm	95.0%
@ 550nm	97.0%
@ 600nm	97.5%
@ 633nm	97.0%
@ 635nm	97.0%
@ 650nm	96.5%
@ 670nm	96.0%
@ 675nm	95.0%
@ 700nm	94.5%

QUOTE YOUR SIZE

COMPATIBLE MOUNTS
