

[See all 23 Products in Family](#)

6", White, UltraSeal Washdown Bar Light

See More by [Advanced Illumination](#)



Advanced Illumination UltraSeal Washdown Bar Lights

Stock **#18-623** CLEARANCE **1 In Stock**

-

1

+

£680^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	£680.00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
AL247M06-WHIIIC	Model Number:
50000	LED Lifetime (hours):
LED Illuminator	Type of Illumination:
Note: Optional Manual Intensity Adjustment #86-887 and #89-555 are Available	

Advanced Illumination	Manufacturer:
Bar Light	Geometry:

Constant	Illumination Mode:
----------	--------------------

Physical & Mechanical Properties

171.4 x 42.9 x 24	Dimensions (mm):
417	Weight (g):

Optical Properties

White	Color:
-------	--------

Electrical

0.35A	Minimum Input Current:
-------	------------------------

Hardware & Interface Connectivity

Flying Leads	Connector:
24V	Input Voltage (V):

Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #89-513 Korea: #33-773 China: #66-855

Environmental & Durability Factors

0 - 60	Operating Temperature (°C):
IP69K	Environmental Rating:

Regulatory Compliance

Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	Reach 233:

Product Details

- IP69K Certified for Extreme Washdown Environments
 - Stainless Steel Housing
 - High Intensity Output up to 70,200 Lux
 - Optional Manual Intensity Adjustments ([#86-887](#) and [#89-555](#)) Recommended
- Advanced Illumination UltraSeal Washdown Bar Lights offer intense, direct illumination up to 70,200 Lux while providing maximum protection in extreme environmental conditions. These IP69K certified Bar Lights were designed with a crevice-free design to withstand high temperature wash-down procedures and material buildup. The 316 stainless steel is FDA compliant, making them a suitable option for food or pharmaceutical inspection environments. Advanced Illumination UltraSeal Washdown Bar Lights are ideal for hygienic and aseptic manufacturing applications, such as prolonged liquid immersion and high-pressure steam cleaning common in food and beverage inspection and processing.
- Note:** Requires 24V power supply [#66-855](#). Manual Intensity Adjustment [#86-887](#) and [#89-555](#) are recommended and sold separately.