

TECHSPEC® 6 x 8.5mm Enhanced Aluminum, 4-6λ Mirror



Stock **#43-867** ☐ In Stock

-

1

+

£20.40

ADD TO CART

Qty 1-5
£20.40

Qty 6+
£15.72

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Flatness (P-V):
4 - 6λ

Substrate: ☐
Float Glass

Surface Quality:
60-40

Dimensions (mm):

6.0 x 8.5
Dimensional Tolerance (mm): ±0.25
Coating Specification: R _{avg} ≥95% @ 450 - 650nm @ 45°
Coating: Enhanced Aluminum (450-650nm)
Coating Type: Metal
Clear Aperture CA (mm): 5.00 x 7.50
Edges: Seamed, 0.5mm Maximum Edge Chip
Thickness (mm): 2.00
Type: Flat Mirror
Wavelength Range (nm): 450 - 650
Length (mm): 8.50
Width (mm): 6.00
Damage Threshold, By Design: ☐ 0.2 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant