See all 18 Products in Family

TECHSPEC® 6.25mm Inner Single Optic Mount

6.25mm Inner Single Optic Mount

Stock **#38-746** **6 In Stock**

- 1 +

£32.80

ADD TO CART

Volume Pricing	
Qty 1-4	**£32.80** each
Qty 5+	**£31.20** each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:
Fixed

Function:
Optic Mount (Fixed)

Physical & Mechanical Properties

Total Length (mm):
9.0

Min. Thickness of Compatible Optics (mm):
1.0

Max. Thickness of Compatible Optics (mm):
4.0

Clear Aperture CA (mm):
5.2

Construction:
Matte Black Anodized Aluminum (6061-T6)

Edge Thickness of Compatible Optics (mm):
4.0

Threading & Mounting

Thread Type:
M29 x 0.75

Diameter of Compatible Optics (mm):
6.25

Regulatory Compliance

RoHS 2015:
Compliant

Certificate of Conformance:
View

Reach 250:
Compliant

Product Details

- Mounts for a Variety of Optical Component Diameters and Thicknesses
- M29 Outer Diameter Threads Allow Easy Positioning Within **Outer Tubes**
- One Retainer Ring and One Delrin Ring are Included
- Click **Here** to See How to Use the Multi-Element Tube System Components to Build an Optical System.

TECHSPEC® Multi-Element Inner Single Optic Mounts are designed to mount a variety of optical components. The mounts support optical diameters from 5mm to 25.4mm, and edge thicknesses of 4mm to 17mm. With M29 x 0.75 outer diameter threads, these mounts can be easily positioned along the optical axis of our TECHSPEC® Multi-Element Outer Tubes. TECHSPEC® Multi-Element Inner Single Optic Mounts include one Delrin ring to ensure secure clamping force between the retainer ring and optic without damaging the optic.

Note: Our specially designed ME Spanner Wrench (**#13-567**) is highly recommended to move Inner Single Optic Mounts back and forth smoothly utilizing a combined metric and English graduated scale. The hollow design enables transmission of output beam while adjusting lens position. Non-scaled ME Spanner Wrench (**#11-046**) is also available.

;