


TECHSPEC<sup>®</sup> 600 x 1000mm Linear Polarizing Film (XP42-18) with Adhesive



Stock #29-491 7 In Stock

-

1

+

£352.00

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-10       | £352.00 each                  |
| Qty 11-25      | £309.28 each                  |
| Need More?     | <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Linear Polarizer

Type:

Note:  
Polarization axis is parallel to first listed dimension

Physical & Mechanical Properties

600.0 x 1000.0 +5.0/0.0

Dimensions (mm):

|                                                                       |                              |
|-----------------------------------------------------------------------|------------------------------|
| 0.22 ±0.03                                                            | Thickness (mm):              |
| Polarizing Film                                                       | Construction:                |
| Optical Properties                                                    |                              |
| Pressure Sensitive Adhesive (PSA) one-sided                           | Coating:                     |
| 9000:1 (nominal at 555nm)                                             | Extinction Ratio:            |
| Polymer Film XP42-18                                                  | Substrate: □                 |
| Single: 42 ±2<br>Parallel: 36.4<br>Crossed: <0.004 (nominal at 555nm) | Transmission (%):            |
| 400 - 700                                                             | Wavelength Range (nm):       |
| >99.98 (nominal at 555nm)                                             | Polarization Efficiency (%): |
| 42 ±2                                                                 | Transmission, Single (%):    |
| 36.4                                                                  | Transmission, Parallel (%):  |
| <0.004 (nominal at 555nm)                                             | Transmission, Crossed (%):   |
| Regulatory Compliance                                                 |                              |
| Compliant                                                             | RoHS 2015:                   |
| View                                                                  | Certificate of Conformance:  |
| Compliant                                                             | Reach 247:                   |

Product Details


- High Transmission of Unpolarized Light from 400 – 700nm
  - Excellent Extinction Ratio of 9000:1
  - Available in Custom Sizes
  - [High-Temperature](#) Options Also Available
- Ideal for a range of imaging applications, TECHSPEC® High Contrast Linear Polarizing Film (XP42) features an excellent extinction ratio and high transmission from 400 – 700nm. This polarizing film is offered in multiple thicknesses; thicker polarizing film has increased rigidity. Available in sheets, TECHSPEC® High Contrast Linear Polarizing Film (XP42) can be cut to fit any application need.


**Note:** Polarizer Film with adhesive available.

Immediate Custom Quotes Available

If you have a need for any round, square, or rectangular size of a TECHSPEC High Contrast Linear Polarizing Film (XP42) in dimensions between 3mm and 600mm, please visit our [Polarizing Film Tool](#). We'll provide an immediate quote, and can deliver the part to your requested size in approximately 3 weeks. A full list of standard manufacturing tolerances and restrictions are listed. For fully customized polymer polarizers to your requirements, visit our [Customized Polymer Polarizers Capabilities](#) page.

Technical Information





;