

LightPath 354220 | 633nm Alignment, 0.25 NA Fiber Collimator w/ FC/PC Connector

See More by [Lightpath®](#)



Fiber Optic Collimator and Focuser Assemblies



Stock **#67-720** 3-4 DAYS



1



£153.00

ADD TO CART

Qty 1-10

£153.00

Qty 11+

£134.72

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Effective Focal Length EFL (mm):
11.00 @ 633nm

Numerical Aperture NA:
0.25

Substrate: D-ZK3
Coating: BBAR (600-1050nm)
Coating Specification: Rabs <1.0% @ 600 - 1050nm
Surface Quality: 40-20
Clear Aperture CA (mm): 5.50
f#: 2.00
Bevel: Protective bevel as needed
Connector: FC/PC
Construction: 304L Stainless Steel Housing
Housing Diameter (mm): 11.00
Housing Length (mm): 17.1
Lightpath Lens Code: 354220
Mount: M11 x0.5
Type: Fiber Collimator
Wavelength Range (nm): 600 - 1050
Conjugate Distance: Infinite
Lens Included: #87-118
Alignment Wavelength (nm): 633

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant