

**TECHSPEC® 6.35 x 6.35mm 266nm 45°, Nd:YAG Laser Line Mirror**



TECHSPEC® Nd:YAG Laser Line Mirrors

Stock **#39-576** **13 In Stock**

⊖ 1 ⊕ £112<sup>00</sup>

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | £112.80 each                  |
| Qty 6-25       | £98.40 each                   |
| Need More?     | <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Laser Mirror Type:

**Physical & Mechanical Properties**

<3 Parallelism (arcmin):

85 Clear Aperture (%):

|  |  |
|--|--|
| Commercial Polish  | <b>Back Surface:</b>   |
| 6.35 x 6.35 +0.00/-0.10  | <b>Dimensions (mm):</b>                                      |
| 3.18 ±0.20   | <b>Thickness (mm):</b>                                       |
| <b>Optical Properties</b>  |  |
| 10-5   | <b>Surface Quality:</b>                                      |
| 99.5   | <b>Reflection at DWL (%):</b>                                |
| R <sub>abs</sub> >99.5% @ 266nm<br>R <sub>avg</sub> >99.5% @ 263 - 268nm | <b>Coating Specification:</b>                                |
| 263 - 268  | <b>Wavelength Range (nm):</b>                                |
| λ10  | <b>Surface Flatness (P-V):</b>                               |
| Dielectric   | <b>Coating Type:</b>   |
| Laser Mirror (263-268nm)   | <b>Coating:</b>  |
| 266  | <b>Design Wavelength DWL (nm):</b>                           |
| 45   | <b>Angle of Incidence (°):</b>                               |
| <a href="#">Fused Silica</a> (Coming 7980)                               | <b>Substrate:</b> <input type="checkbox"/>                   |
| 2.5 J/cm <sup>2</sup> @ 266nm, 20ns, 20Hz                                | <b>Damage Threshold, Reference:</b> <input type="checkbox"/> |

|                              |                                    |
|------------------------------|------------------------------------|
| <b>Regulatory Compliance</b> |                                    |
| <a href="#">Compliant</a>    | <b>RoHS 2015:</b>                  |
| <a href="#">Compliant</a>    | <b>Reach 209:</b>                  |
| <a href="#">View</a>         | <b>Certificate of Conformance:</b> |

## Product Details

- Up to 99.9% Reflectivity at Nd:YAG Harmonic Frequencies
- High Laser Induced Damage Threshold Specifications
- 10-5 Surface Quality for Reduced Scatter in Sensitive Laser Applications
- [TECHSPEC® Laser Mirror Substrates](#) and [TECHSPEC® Yb:YAG Laser Line Mirrors](#) Also Available

TECHSPEC® Nd:YAG Laser Line Mirrors combine high reflectivity, excellent surface quality, and precision surface flatness to meet the requirements of demanding Nd:YAG laser applications. Each coating design has been tested to ensure a high laser damage threshold for compatibility with pulsed laser systems. These fused silica substrate laser mirrors have excellent thermal stability and are available in round, square, and rectangular profiles. TECHSPEC® Nd:YAG Laser Line Mirrors are ideal for laboratories and integration into larger laser systems. 266nm, 355nm, 532nm, 1064nm, and multi-line Nd:YAG mirror coatings are available.

**Note:** Contact us for customizable wavelengths, sizes, and varying AOI versions.

## Compatible Mounts

;