

TECHSPEC[®] 6.35mm Dia. x 76.2mm EFL, UV Enhanced Aluminum 50Å 90° Off-Axis Mirror



TECHSPEC Aluminum Off-Axis Parabolic Mirrors

Stock **#37-292** CLEARANCE **1 In Stock**

☐ [Other Coating Options](#)

-

1

+

£168^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	£168.00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Off-Axis Parabolic Mirror	Type:
Physical & Mechanical Properties	
6.35 +0.1/-0.0	Diameter (mm):
<50 RMS	Surface Roughness (□):

76.20	Y Offset (mm):
Optical Properties	
76.20	Effective Focal Length EFL (mm):
±1	Focal Length Tolerance (%):
76.20	Radius of Curvature (mm):
Enhanced Aluminum (250-700nm)	Coating:
Metal	Coating Type:
R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	Coating Specification:
90	Off-Set Angle (°):
38.1	Parent Focal Length PFL (mm):
λ/8	Surface Figure, RMS:
250 - 700	Wavelength Range (nm):
80-50	Surface Quality:
Aluminum 6061-T6	Substrate:
λ/4	Reflected Wavefront, RMS:

Threading & Mounting	
#37-943	Compatible Mounting Plates:

Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	REACH 201:
View	Certificate of Conformance:

Product Details

• Aluminum Coatings for UV, Visible, and NIR Applications


• Range of Surface Roughness, Including 50Å and 100Å

• 15°, 30°, 45°, 60°, or 90° Offset Angle Options

• Gold and Silver Coated Off-Axis Parabolic Mirrors Also Available

TECHSPEC® Aluminum Off-Axis Parabolic Mirrors (OAPs) are a cost-effective solution for focusing incident light with minimal scatter loss. Available with enhanced or protected aluminum coatings, these OAP mirrors offer high reflectivity from the ultraviolet (UV) to the near infrared (NIR). These Aluminum OAPs are manufactured with multiple surface roughness specifications, offering designers the choice between high performance, low scatter mirrors and more cost sensitive options. TECHSPEC® Aluminum Off-Axis Parabolic Mirrors are used in optical systems such as Schlieren and spectroscopy systems, as well as in laser systems to focus laser beams. For increased system integration flexibility, mounting plates that thread to the base of these off-axis parabolic mirrors are available.

Technical Information



Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).
