

[See all 102 Products in Family](#)

6.5mm Diameter x 6mm FL, MgF₂ Coated, PCX Condenser Lens



Stock **#15-527** **2 In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ £33²⁰

ADD TO CART

Volume Pricing

Qty 1-10	£33.20 each
Qty 11-49	£30.40 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Condenser Lens **Type:**

Physical & Mechanical Properties

6.50 **Diameter (mm):**

3.75 ±0.1 **Center Thickness CT (mm):**

Protective as needed	Bevel:
Plano	Shape of Back Surface:
Optical Properties	
6.00	Effective Focal Length EFL (mm):
0.58	Numerical Aperture NA:
Float Glass	Substrate: <input type="checkbox"/>
±7	Focal Length Tolerance (%):
MgF ₂ (400-700nm)	Coating:
R _{avg} ≤ 1.75% @ 400 - 700nm	Coating Specification:
80-50 (typical)	Surface Quality:
0.86	f#:
Plano	Radius R₂ (mm):
400 - 700	Wavelength Range (nm):
Infinite	Conjugate Distance:


Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

Product Details

- Molded Illumination Lenses
- Aspheric or Spherical Designs
- High Numerical Apertures

Condenser Lenses are molded lenses designed for illumination applications. Featuring large apertures and short focal lengths, Condenser Lenses are commonly used in emitter-detector applications, projection applications, or condensing illumination applications such as Koehler Illumination. The Aspheric Condenser Lenses are molded on the aspheric surface and ground and polished on the opposite face, offering superior performance. The Plano-Convex (PCX) Condenser Lenses are molded on both surfaces, offering excellent value.

Technical Information



Coating Curves

