

[See all 64 Products in Family](#)

# Coherent® StingRay™ Line Generator 1231510 | 660nm, 35mW, 60° Fan Angle

See More by [Coherent®](#)



Stock #86-868 **3 In Stock**

- 1 + £573<sup>00</sup>

**ADD TO CART**

#### Volume Pricing

Qty 1+	£573.00 each
Need More?	<a href="#">Request Quote</a>

Prices shown are exclusive of VAT/local taxes

**Note:** This item requires accessories for use | [Learn More](#)

#### Product Downloads



#### General

Coherent® **Manufacturer:**

Diode **Type of Laser:**

**Laser Class - CDRH:**

Illa

Model Number:

1231510

## Physical & Mechanical Properties

Pointing Stability ( $\mu\text{rad}/^\circ\text{C}$ ):

<10

Length (mm):

97.80

## Optical Properties

Spatial Mode:

TEM<sub>00</sub>

Wavelength (nm):

660.00

Mode Quality, M<sup>2</sup>:

<1.5

Wavelength Tolerance (nm):

±5

Color:

Red

Fan Angle (°):

60.00

## Electrical

Output Power (mW):

35

Modulation Frequency (kHz):

Max Analog: 500

## Hardware & Interface Connectivity

Power Supply:

Power Supply Required and Sold Separately:

USA: [#86-878](#)

Europe: [#86-878](#)

Japan: [#86-878](#)

Korea: [#86-878](#)

China: [#86-878](#)

Electrical Leads/ Pin Connections:

Hirose HR-10P-12S

Output Type:

Free Space

Input Voltage (V):

5 - 24 DC

## Environmental & Durability Factors

Operating Temperature (°C):

-10 to +50

Storage Temperature (°C):

-20 to +60

## Regulatory Compliance

RoHS 2015:

[Exempt](#)

Reach 224:

[Contains SVHC\(s\)](#)

Certificate of Conformance:

[View](#)

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

Class IIIa Lasers Require [#62-941](#) Power Supply. Power supply is available with [#86-878](#) or sold separately. These lasers include a Hirose connector and flying lead terminals for compatibility with a variety of power supplies.

- External Focus with up to 100mW Output Power
- Auto Scaling Input Power 5 - 24VDC with Reverse Polarity Protection
- Built-In Microcontroller for Fault Monitor

- [Coherent® StingRay™ Developer's Kit](#) also available

Coherent® StingRay™ and BioRay™ Laser Diode Modules are ideal for a variety of alignment, machine vision, and biomedical applications. They are available in a wide range of output powers, wavelengths, and fan angles. High precision optical components and sophisticated drive electronics provide power and control to your application, reducing signal-to-noise ratios and increasing measurement speed. Coherent® StingRay™ and BioRay™ Laser Diode Modules are designed with a flat top power distribution across the beam profile for consistency in line projection widths.

**Note:** For CDRH certified systems (Class IIIb), [#86-878](#) Laser Controller and additional external voltage source (0.5-5V) with BNC connector is required.

---