

676nm CWL, 11.8mm Dia. Bandpass Filter



Stock #28-484 CLEARANCE 20+ In Stock

⊖ 1 ⊕ £15⁹⁶

[ADD TO CART](#)

Volume Pricing

Qty 1+	£15.96 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Bandpass Filter **Type:**

Kr Emission Line **Typical Applications:**

Physical & Mechanical Properties

11.80 **Diameter (mm):**

4.60 **Thickness (mm):**

±0.2 Dimensional Tolerance (mm):

Optical Properties

≥3.0 Optical Density OD (Average):

676.00 Center Wavelength CWL (nm):

±2 Center Wavelength CWL Tolerance (nm):

10.00 Full Width-Half Max FWHM (nm):

50 Minimum Transmission (%):

80-50 Surface Quality:

200 - 1200 Blocking Wavelength Range (nm):

Regulatory Compliance

[View](#) Certificate of Conformance:

Product Details

- Ideal for Selectively Transmitting a Narrow Range of Wavelengths
- Quantities Extremely Limited, Buy While Supplies Last
- For Even More Deals, Check out [Mega Clearance: Optics](#)

Bandpass interference filters are used extensively in a variety of biotech, biomedical, or quantitative chemical applications to selectively transmit a narrow range of wavelengths while blocking all others. Experimental Grade Bandpass Interference Filters are available in a variety of bandpass ranges in 11.8mm and 24.15mm diameter unmounted options.

Note: Specifications for experimental grade optics may vary as much as 10% from those listed. Also, no additional information is available other than what is provided.

Technical Information

