

TECHSPEC[®] 6.25mm Dia x -10mm FL VIS 0° Coated, Negative Achromatic Lens



Stock **#62-478** [CONTACT US](#)
[Other Coating Options](#)

-

1

+

£62.05

ADD TO CART

Qty 1-5
£62.05
Qty 6+
£52.70
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
6.25 +0.0/-0.025

Effective Focal Length EFL (mm):

-10.00
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): -11.92
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 5.625
Centering (arcmin): <3
Center Thickness CT (mm): 3.50 ±0.10
Center Thickness CT 1 (mm): 1.00 ±0.05
Center Thickness CT 2 (mm): 2.50 ±0.05
Radius R₁ (mm): -6.55
Radius R₂ (mm): 5.10
Radius R₃ (mm): 89.10
Edge Thickness ET (mm): 4.19
Substrate:  N-BAF10 / N-SF10
Surface Quality: 40-20
f/#: 1.6
Numerical Aperture NA: 0.31
Coating: VIS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Negative Achromatic Lens
Wavelength Range (nm): 425 - 675

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View