

632.8nm, 1mW Fiber-Coupled Frequency Stabilized Laser Diode



632.8nm Frequency Stabilized Laser Diodes (Free Space and Fiber-Coupled options shown)

Stock **#73-776** 1 In Stock

-

1

+

£6,800⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£6,800.00 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads



General	
2.00	Warm-Up Time (minutes):
Single Mode w/3mm Dia Stainless Steel Shielding	Fiber Cable Type:
Diode	Type of Laser:
IIIb	Laser Class - CDRH:

Physical & Mechanical Properties	
71.0 L x 63.5 W x 19.8 H	Dimensions (mm):
135.00	Weight (g):
1	Length of Fiber (m):
<50 (8 Hours)	Pointing Stability (μrad):
Optical Properties	
0.13	Numerical Aperture NA:
4.3 MFD	Fiber Diameter (μm):
632.80	Wavelength (nm):
±0.5	Wavelength Tolerance (nm):
±0.002	Beam Stability (nm):
Red	Color:
<100	Spectral Line Width (KHz):
Electrical	
1	Output Power (mW):
1.00	Power Stability (%):
Max 5	Power Consumption (W):
±20	Output Power Tolerance (%):
10 Hz - 100 MHz 0.2% RMS	Noise Level:
Max 2 @ 3.3 V	Input Current (A):
Hardware & Interface Connectivity	
10-pin Connectors (cable provided upon request)	Electrical Leads/ Pin Connections:
USB	Computer Interface:
Fiber-Coupled	Output Type:
FC/APC	Connector:
Environmental & Durability Factors	
+15 to +40	Operating Temperature (°C):
5 - 95% (non-condensing)	Operating Humidity:
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Single Longitudinal Mode (SLM) Performance
- ±0.002nm Wavelength Stability
- Very Low Power Consumption

632.8nm Frequency Stabilized Laser Diodes are ideal for typical HeNe laser applications including flow cytometry, interferometry, confocal microscopy, fluorescence excitation, and Raman spectroscopy. Whereas a comparable HeNe laser would be larger, more expensive, and consume more power, the 632.8nm Frequency Stabilized Laser Diodes feature more compact designs, ±0.002nm wavelength stability, and either greater than 60mW power (free-space model) or greater than 20mW power (fiber coupled model). Additionally, these lasers utilize Variable Bragg Gratings (VBG) to lock the 632.8nm wavelength to a 10MHz linewidth.