

[See all 40 Products in Family](#)

63.5mm Length, M6 and M6, Steel Post



Stock #72-774 NEW 17 In Stock

- 1 + £5^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	£5.00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

	Type:
Metric	

Physical & Mechanical Properties

	Length Tolerance (mm):
±0.1	
	Length (inches):
2.5	
	Length (mm):
63.50	

0.5	Diameter (inches):
12.70	Diameter (mm):
-0.02/-0.05	Diameter Tolerance (mm):

Threading & Mounting

Thread 1: M6 x 1 Thread 2: M6 x 1	Male Thread:
--------------------------------------	--------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:

Compliant	Reach 247:
---------------------------	------------

Product Details

- English or Metric Versions Options Available
- Wide Variety of Lengths Available from 25.4 to 304.8mm (1" to 12").
- Removable Top and Bottom Set Screws Available

Stainless Steel Optical Mounting Posts are a practical and straightforward way to integrate optical assemblies and photonic equipment onto an [optical lab table](#) or [breadboard](#). All mounting posts are 12.7 mm (0.5") in diameter and are offered in various lengths from 25.4 to 304.8mm (1" to 12"). Each mounting post features a female thread on each end with a set screw preinstalled, making it simple to mount components with counterbore or tapped hole mounting features. Stainless Steel Optical Mounting Posts can be used with [Post Holders](#) to allow for height adjustment of the optical component, and for a secure connection with the optical benchtop. Thread values (M4 x 0.7/M6 x 1.0 for Metric; 8-32/¼-20 for English) are laser-engraved on the ends of each post for quick identification and integration.

Note: All posts have a through-hole that allows an Allen wrench, 5.5mm or 7/32" key size, or other tools to rotate the post easily.