

TECHSPEC® 6mm Dia. x 6mm FL, VIS 0° Inked, Double-Convex Lens



Stock **#47-478-INK** 3-5 DAYS
[Other Coating Options](#)

- 1 + **£42.07**

ADD TO CART

Qty 1-9
£42.07
Qty 10+
£37.82
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
6.00 ±0.025

Back Focal Length BFL (mm):

5.19
Effective Focal Length EFL (mm): 6.00
Coating: VS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Substrate: ☐ N-SF5
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <3
Bevel: Protective bevel as needed
Center Thickness CT (mm): 2.54
Center Thickness Tolerance (mm): ±0.05
Edge Thickness ET (mm): 1.29
Radius R₁=R₂ (mm): 7.59
Clear Aperture CA (mm): 5.4
f/#: 1.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.50
Type: Double-Convex Lens
Wavelength Range (nm): 425 - 675
Damage Threshold, By Design: ☐ 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View