

TECHSPEC® 6mm, f/2.8 Sealed UCw Series Fixed Focal Length Lens



UCw Series Fixed Focal Length Lenses

Stock #70-589 NEW 2 In Stock

-

1

+

£208²⁵

ADD TO CART

Volume Pricing	
Qty 1+	£208.25 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Ucw Series

Series:

Fixed Focal Length Lens

Type:

Imaging Lens Type: High Performance Lens with Compact Form Factor	
Physical & Mechanical Properties	
Fixed	Iris Option:
40.10	Length (mm):
38	Maximum Diameter (mm):
38	Outer Diameter (mm):
3.82	Maximum Rear Protrusion (mm):
40.9	Maximum Length (mm):
Optical Properties	
60.0°	Horizontal Field of View @ Max Sensor Format:
60.0°	Horizontal Field of View, 1/2" Sensor:
54.6°	Horizontal Field of View, 1/2.5" Sensor:
45.4°	Horizontal Field of View, 1/3" Sensor:
34.2°	Horizontal Field of View, 1/4" Sensor:
8.00	Maximum Image Circle (mm):
0.02	Numerical Aperture NA, Object Side:
9 (8)	Number of Elements (Groups):
6.00	Focal Length FL (mm):
50 - ∞	Working Distance (mm):
f/2.8	Aperture (f/#):
λ/4 MgF ₂	Coating:
λ/4 MgF ₂	Coating Specification:
12.61	Entrance Pupil Position (mm):
17.55	Object Space Principal Plane (mm):
4.85	Image Space Principal Plane (mm):
-11.19	Maximum Distortion (%):
-23.26	Exit Pupil Position (mm):
VS	Lens Wavelength Range:
Sensor	
1/2.5"	Optimized Sensor Format:
1/2"	Maximum Sensor Format:
Threading & Mounting	
M34 x0.5 (Female)	Filter Thread:
M34 x0.5 (Female)	Front Thread:
C-Mount	Mount:
Environmental & Durability Factors	
IPX7	Environmental Rating:

Storage Temperature (°C): -20 to +60 For questions regarding operating temperature please contact our support team	
Type of Ruggedization: Waterproof (IPX7)	

Regulatory Compliance	
Certificate of Conformance: View	

PRODUCT DETAILS

- Up to 1/2", C-Mount Lens
- Ultra-Compact (UC), High Resolution Lens for Small Sensors
- Waterproof Versions of UC Series Fixed Focal Length Lenses
- Meets IEC Ingress Protection Ratings of IPX7

TECHSPEC® UCw Series Fixed Focal Length Lenses are waterproof versions of our [TECHSPEC® UC Series Fixed Focal Length Lenses](#), and are designed to meet IEC Ingress Protection Codes IPX7 to withstand exposure to water up to 1 meter depth for 30 minutes. Additionally, their compact size provides high performance at an affordable cost without sacrificing quality or feel. These lenses include a hydrophobic coated window to prevent water droplets from settling on the lens' surface and are sealed with multiple O-rings to prevent moisture from entering the housing. TECHSPEC® UCw Series Fixed Focal Length Lenses are ideal for applications in space constrained, harsh environments such as food inspection, security, medical, and factory automation.

Edmund Optics has created a family of high-performance ultra-compact optical designs (the UC Series family) and developed 3 customized optomechanical solutions targeted for specific applications. These lens sub-families utilize the same optics as the UC Series lenses providing the same optical performance in a variety of optomechanical solutions to meet your application requirements:

UC Series: Features locking cam focus and iris adjustment in an ultra-compact design and is the most adjustable version of these optical designs; they are the typical high-quality machine vision lenses.

UCi Series: Simplified mechanics featuring fixed apertures with compact housing. [Industrial Ruggedization](#) for reduced size, cost, and locked focus.

UCr Series: All optics glued in place and a locking C-clamp focus ring. [Stabilized Ruggedization](#) for reduced pixel shift and improved focus stability.

UCw Series: Waterproof, designed to meet IEC [Ingress Protection](#) Code IPX7 to withstand exposure to water up to 1 meter depth for 30 minutes.