

[See all 11 Products in Family](#)

6" White Advanced Illumination High Intensity Ring Light

See More by [Advanced Illumination](#)



Stock #88-490 [CONTACT US](#)

⊖ 1 ⊕ £1,120⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	£1,120.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General

RL113-WHI-C **Model Number:**

50,000 **LED Lifetime (hours):**

Number of Channels:

1.00

LED Illuminator

Type of Illumination:

Note:

Optional Manual Intensity Adjustment [#86-887](#) and [#89-555](#) are Available

Advanced Illumination

Manufacturer:

Ring Light

Geometry:

Constant

Illumination Mode:

Physical & Mechanical Properties

152.40

Diameter (mm):

26.7

Height (mm):

66.00

Inner Diameter (mm):

152.4

Outer Diameter (mm):

681.00

Weight (g):

Optical Properties

White

Color:

225 - 600

Working Distance (mm):

Hardware & Interface Connectivity

Flying Leads

Connector:

Power Supply Required and Sold Separately.

Power Supply:

USA: [#66-855](#)
Europe: [#66-855](#)
Japan: [#89-513](#)
Korea: [#33-773](#)
China: [#66-855](#)

Environmental & Durability Factors

0 to 60

Operating Temperature (°C):

IP67

Environmental Rating:

Regulatory Compliance

[Compliant](#)

RoHS 2015:

[View](#)

Certificate of Conformance:

[Contains SVHC\(s\)](#)

Reach 233:

Product Details

- Slim Profile to Ease System Integration
- High Brightness LEDs
- Multiple Size, Wavelength, and Working Distance Options

Advanced Illumination High Intensity Ring Lights utilize an arrangement of high brightness LEDs to precisely illuminate a wide variety of imaging applications. Advanced Illumination High Intensity Ring Lights feature a slim profile to ease system integration, and are available in a variety of sizes, wavelengths, and working distance options. A manual intensity adjustment option is also available for added flexibility. 4.6" and 6" models are IP67 compliant. An adapter is also available for mounting the 2.95" ring light to M25 x0.5 lenses.

Note: Required 24V power supply [#66-855](#). [Accessories for Advanced Illumination products](#) are available and sold separately.

3D-Printable Mount Files



Ring Light Configuration

[Download Now](#)

Designed for use with the [Articulating Arm Mounting Systems](#), these 3D-printed mounts allow easy positioning of lights in brightfield or darkfield setups. The design is based on mounting illumination to 1/4-20" breadboards or into 80/20 extrusion systems, but can be adapted based on user needs. Mounts are available for ring, bar, line, and inline spot lights.



[Application Note](#)

[Illumination Mounts for Machine Vision Applications](#)

[Read](#)



[Video](#)

[Assembly of 3D Printed Mounts for Common Illumination Geometries](#)

[Watch](#)