

[See all 16 Products in Family](#)

70mm Precision Stage, Metric Dovetail Carrier



70mm Precision Stage, Metric Dovetail Carrier

Stock **#12-511** 20+ In Stock

-

1

+

£121⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-9	£121.60 each
Qty 10+	£107.84 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Metric	Type:
Carrier	Note:
Physical & Mechanical Properties	
Linear (X)	Type of Movement:

	Guide System:
Dovetail	
	Length (inches):
2.76	
	Length (mm):
70.00	
	Construction:
Black Anodized Aluminum	

Hardware & Interface Connectivity

	Type of Drive:
Manual	

Threading & Mounting

	Mounting Threads:
(4) M3 x 0.5, (8) M2 x 0.4, (9) M6 x 1.0	

Regulatory Compliance

	RoHS 2015:
Compliant	
	Certificate of Conformance:
View	
	REACH 241:
Compliant	

Product Details

- Wide Range of Carrier Length and Mounting Hole Options Available
- Low Profile Design with Smooth Movement
- Increased Stability and <1mrad Straight Line Accuracy

Dovetail Optical Rail Systems are designed for easy and stable installation and positioning of various optical components along the same axis. The rails feature slotted holes that allow them to be fixed to standard 1/4-20 TPI and M6 breadboards or optical tables. Carriers are available with different lengths and hole patterns to meet various mounting needs including options that are directly compatible with our [TECHSPEC® Manual Stages](#) for precision alignment. Carriers utilize a unique two-piece design to prevent the locking screws from contacting the rail and to allow easy attachment and removal. All Dovetail Optical Rail System parts are constructed of black anodized aluminum to minimize stray reflections or glare.

Note: Rails and carriers are sold separately.

Technical Information





Figure 1: Detail of reinforcement layout. The diagram shows a rectangular cross-section of a concrete slab with dimensions 2.50m in height and 1.00m in width. The reinforcement layout includes top bars (circles) and bottom bars (squares). Dimensions for bar spacing are given: 0.25m for the top bar spacing, 1.25m for the bottom bar spacing, and 1.00m for the width. A note indicates "1/4-20 top 9 places".

Technical drawing of a rectangular plate with the following specifications:

- Overall width: 1.75
- Overall height: 2.00
- Top edge hole: M2 x 0.4 thru, 4 places
- Bottom edge hole: M3 x 0.5 thru, 4 places
- Central hole: M16 x 1.0 thru
- Horizontal spacing from left edge to central hole: 0.787 typ
- Horizontal spacing from right edge to central hole: 0.787 typ
- Vertical spacing from top edge to central hole: 1.26 typ
- Vertical spacing from bottom edge to central hole: 1.26 typ



Stock No.	L	A	B	C	D	# Slots	# C'bores
#54-401	12	6	4	—	—	3	—
#54-402	36	18	16	4	6	5	2

