

## 70mm Sq. Metric Kinematic Magnetic Base



#22-404: 70mm Sq. Metric Kinematic Magnetic Base

Stock **#22-404** **2 In Stock**

⊖ 1 ⊕ £123<sup>20</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-9	£123.20 each
Qty 10+	£111.44 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Type:  
Metric

Switchable:  
No

### Physical & Mechanical Properties

Length (mm):  
70.00

70.00	<b>Width (mm):</b>
25.40	<b>Thickness (mm):</b>
Anodized Aluminum	<b>Construction:</b>
0.27	<b>Weight (kg):</b>
<70.0	<b>Repeatability (µrad):</b>

## Threading & Mounting

(8) M4 x 0.7, (11) M6 x 1.0	<b>Mounting Threads:</b>
-----------------------------	--------------------------

## Material Properties

20	<b>Magnetic Force (N):</b>
----	----------------------------

## Regulatory Compliance

<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>Reach 247:</b>

## Product Details

- Common 25.4mm (1") Platform Height
- Removable Top Plates with High Repeatability Kinematic Positioning
- Compatible with all with [TECHSPEC Stages](#)

Kinematic Magnetic Base Plates are ideal for simplifying the adjustment of subsystems in a benchtop optical system. The bases feature a common platform height of 25.4mm (1") to allow for simplified optical axis alignment. Each base has a removeable top plate, ideal for adding or removing system components and subassemblies anywhere on a lab table with ease. Internal kinematic positioning allows the top plates to be removed and replaced with high repeatability. Kinematic Magnetic Base Plates are directly compatible with our [TECHSPEC stages](#), making them an ideal lab bench component for system building.