

TECHSPEC® 75mm C Series Fixed Focal Length SWIR Lens



Stock #74-055 **NEW** [CONTACT US](#)

- 1 + £383.00

ADD TO CART

Volume Pricing	
Qty 1+	£383.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Product Family:
C SWIR Series

Type:
Fixed Focal Length Lens

Imaging Lens Type:
Compact Lens Coated for Visible to Near Infrared

Physical & Mechanical Properties

Variable	Iris Option:
98.76	Length (mm):
48.0	Maximum Diameter (mm):
48.0	Outer Diameter (mm):
362	Weight (g):
7.24	Maximum Rear Protrusion (mm):

Optical Properties

5.76°	Horizontal Field of View @ Max Sensor Format:
	Field of View at Max Sensor Format: Horizontal: 5.76° Vertical: 4.32° Diagonal: 7.19°
5.76°	Horizontal Field of View, 2/3" Sensor:
4.71°	Horizontal Field of View, 1/1.8" Sensor:
4.19°	Horizontal Field of View, 1/2" Sensor:
3.77°	Horizontal Field of View, 1/2.5" Sensor:
3.14°	Horizontal Field of View, 1/3" Sensor:
11.00	Maximum Image Circle (mm):
0.05111	Numerical Aperture NA, Object Side:
7 (6)	Number of Elements (Groups):
75.00	Focal Length FL (mm):
500 - ∞	Working Distance (mm):
f/2.0 - f/16.0	Aperture (f/#):
900 - 1700nm BBAR	Coating:
900 - 1700nm BBAR	Coating Specification:
63.265	Entrance Pupil Position (mm):
-15.01	Object Space Principal Plane (mm):
-64.79	Image Space Principal Plane (mm):
0.068	Maximum Distortion (%):
-31.983	Exit Pupil Position (mm):
SWIR	Lens Wavelength Range:
SWIR	Wavelength:

Sensor

2/3"	Maximum Sensor Format:
------	-------------------------------

Threading & Mounting

M43 x 0.75 (Female)	Filter Thread:
C-Mount	Mount:

Environmental & Durability Factors

-20 to +60 For questions regarding operating temperature please contact our support team	Storage Temperature (°C):
--	----------------------------------

Certificate of Conformance:

[View](#)

Product Details

- Up to 2/3", C-Mount Lens
- Up to 7.5 MegaPixels, 2.8µm Pixel Size Sensors
- Compact (C) SWIR Lens for 900-1700nm Wavelength Range
- 3.5mm to 100mm Focal Length

TECHSPEC® C Series Fixed Focal Length **SWIR** Lenses are compact, lightweight lenses designed as a low-cost alternative to the **TECHSPEC® SWIR Series Fixed Focal Length Lenses**. These lenses feature large maximum apertures, broadband AR coatings optimized for a 900 – 1700nm wavelength range, and with the working distances and resolution requirements of factory automation and inspection in mind. For optimum resolution and performance at the application's target spectral range, SWIR Machine Vision filters and **SWIR LED illumination** are recommended. TECHSPEC® C Series Fixed Focal Length SWIR Lenses are manufactured to a high tolerance, resulting in greater levels of imaging performance and low lens-to-lens variation, assuring simple installation into multiple systems. Also available with optimized performance in the **VIS** or **VIS-NIR** spectral ranges, C-Series lenses are ideal for a wide variety of machine vision, factory automation, and autonomous applications.

;