

**TECHSPEC® 75mm DG Series Fixed Focal Length Lens**



75mm Focal Length, #54-691

Stock **#54-691** **9 In Stock**

⊖ 1 ⊕ £540.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-49	£540.00 each
Qty 50+	£424.00 each
Need More?	<a href="#">Request Quote</a>

**ⓘ** Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

DG Series **Product Family:**

Fixed Focal Length Lens **Type:**

Traditional Double-Gauss Style Lens **Imaging Lens Type:**

**Physical & Mechanical Properties**

Variable	<b>Iris Option:</b>
116.20	<b>Length (mm):</b>
47.5	<b>Maximum Diameter (mm):</b>
47.5	<b>Outer Diameter (mm):</b>
436	<b>Weight (g):</b>
3.5	<b>Maximum Rear Protrusion (mm):</b>

## Optical Properties

<b>Horizontal Field of View @ Max Sensor Format:</b>	
55.4mm - 13.2°	
<b>Field of View at Max Sensor Format:</b>	
Horizontal: 53mm - 13.2°	
Vertical: 39.7mm - 9.9°	
Diagonal: 66.2mm - 16.4°	
<b>Horizontal Field of View, 4/3" Sensor:</b>	
55.4mm - 13.2°	
<b>Horizontal Field of View, 1.1" Sensor:</b>	
45.4mm - 10.8°	
<b>Horizontal Field of View, 1" Sensor:</b>	
40.9mm - 9.8°	
<b>Horizontal Field of View, 2/3" Sensor:</b>	
28.1mm - 6.7°	
<b>Horizontal Field of View, 1/1.8" Sensor:</b>	
23.0mm - 5.5°	
<b>Horizontal Field of View, 1/2" Sensor:</b>	
20.5mm - 4.9°	
<b>Horizontal Field of View, 1/2.5" Sensor:</b>	
18.5mm - 4.4°	
<b>Horizontal Field of View, 1/3" Sensor:</b>	
15.3mm - 3.7°	
<b>Horizontal Field of View, 1/4" Sensor:</b>	
11.5mm - 2.8°	
21.60	<b>Maximum Image Circle (mm):</b>
0.0316	<b>Numerical Aperture NA, Object Side:</b>
6 (4)	<b>Number of Elements (Groups):</b>
75.00	<b>Focal Length FL (mm):</b>
250 - ∞	<b>Working Distance (mm):</b>
f/4 - f/30	<b>Aperture (f#):</b>
N4 MgF <sub>2</sub>	<b>Coating:</b>
N4 MgF <sub>2</sub>	<b>Coating Specification:</b>
31.44	<b>Entrance Pupil Position (mm):</b>
39.65	<b>Object Space Principal Plane (mm):</b>
-30.62	<b>Image Space Principal Plane (mm):</b>
0.16	<b>Maximum Distortion (%):</b>
-39.84	<b>Exit Pupil Position (mm):</b>
VIS	<b>Lens Wavelength Range:</b>

## Sensor

4/3"	<b>Maximum Sensor Format:</b>
2.74	<b>Pixel Size (µm):</b>

## Threading & Mounting

M49.0 x0.75 (Female)	<b>Filter Thread:</b>
----------------------	-----------------------

C-Mount **Mount:**

## Environmental & Durability Factors

**Storage Temperature (°C):**  
-20 to +60

## Regulatory Compliance

**RoHS 2015:**  
Exempt

**REACH 201:**  
Compliant

**Certificate of Conformance:**  
View


## Product Details

- Up to 4/3", C-Mount Lens
- Up to 9 MegaPixels, 2.8µm Pixel Size Sensors
- Double Gauss (DG) Lens with low distortion and high performance
- 18mm to 75mm Focal Length


TECHSPEC® DG Series Fixed Focal Length Lenses utilize a Double Gauss design to provide high-performance, low distortion, compact size, and exceptional value, while exceeding the performance of typically available fixed focal length lenses. These lenses feature a mechanical design that allows the focusing movement to be motorized by the user, yields image resolution greater than 100 lp/mm, and have a standard C-Mount. For most applications, the camera-lens combination can be attached to workstations using the 1/4-20 mount provided on the camera. TECHSPEC® DG Series Fixed Focal Length Lenses include focus ring, manual iris, and set screws to facilitate a low profile integration in machine vision applications. Typical applications for the DG Series lenses include machine vision, assembly-line integration, and measurement and image analysis.

**Note:** [Industrial Boom Stands](#) are recommended for building vibration-free workstations.


## Technical Information




#54-691, 75mm DG Series Fixed Focal Length Lens, Distortion Plot




#54-691, 75mm DG Series Fixed Focal Length Lens, Relative Illumination Plot




#54-691, 75mm DG Series Fixed Focal Length Lens, Working Distance versus Field of View Plot




#54-691, 75mm DG Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 250mm Working Distance, f4



#54-691, 75mm DG Series Fixed Focal Length Lens, Depth of Field Plot, 250mm Working Distance, f4



#54-691, 75mm DG Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 500mm Working Distance, f4



#54-691, 75mm DG Series Fixed Focal Length Lens, Depth of Field Plot, 500mm Working Distance, f4

Dimensions							
FL (mm)	A (mm)	B (mm)	C (mm)	D (mm)	E (mm)	F (mm)	Filter Thread (Dia. x Pitch)
18	48.0	32.3	4.6	40.0	-	2.5	M30.5 x 0.5
25	39.0	40.0	5.8	34.7	30.7	2.2	M30.5 x 0.5
35	45.0	50.1	11.6	40.0	42.1	0	M37.0 x 0.75
50	47.5	69.0	10.6	40.0	40.8	0	M39.0 x 0.5
75	54.0	116.2	19.2	46.0	67.7	0	M49.0 x 0.75

## Compatible Cameras