

TECHSPEC[®] 75mm Dia. x 200mm FL, VIS 0°, Inked, Achromatic Lens



Stock **#88-593-INK** [CONTACT US](#)

☐ [Other Coating Options](#)

-

1

+

£318⁴⁰

ADD TO CART

Volume Pricing	
Qty 1-5	£318.40 each
Qty 6-25	£255.20 each
Qty 26-49	£239.20 each
Need More?	Request Quote

!

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Achromatic Lens

Type:

Physical & Mechanical Properties

75.00 ±0.025	Diameter (mm):
73.5	Clear Aperture CA (mm):
<1	Centering (arcmin):
23.94 ±0.20	Center Thickness CT (mm):
17.94 ±0.10	Center Thickness CT 1 (mm):
6.00 ±0.10	Center Thickness CT 2 (mm):
15.42	Edge Thickness ET (mm):
Protective as needed	Bevel:

Optical Properties	
200.00	Effective Focal Length EFL (mm):
±1	Focal Length Tolerance (%):
187.69	Back Focal Length BFL (mm):
587.6	Focal Length Specification Wavelength (nm):
118.81	Radius R ₁ (mm):
-96.37	Radius R ₂ (mm):
-288.97	Radius R ₃ (mm):
N-BK7 / N-SF5	Substrate:
40-20	Surface Quality:
2.67	f/#:
0.19	Numerical Aperture NA:
VIS 0° (425-675nm)	Coating:
R _{avg} ≤0.4% @ 425 - 675nm	Coating Specification:
1.5λ	Power (P-V) @ 632.8nm:
λ/4	Irregularity (P-V) @ 632.8nm:
425 - 675	Wavelength Range (nm):

Regulatory Compliance	
View	Certificate of Conformance:

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume


Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Designed for 0° Angle of Incidence
- Less Than 0.4% Reflectance Per Surface from 425 - 675nm
- **MgF₂** and **VIS-NIR** Coated Achromats Also Available

TECHSPEC® VIS 0° Coated Achromatic Lenses consist of two optical components cemented together to form an achromatic doublet. The doublet is computer optimized to correct for on-axis spherical and chromatic aberrations. Achromatic lenses are best for applications involving multi-color (white light) imaging due to their specific doublet lens pairing that enables them to correct the color separation inherent in glass. TECHSPEC® VIS 0° Coated

Technical Information



Coating Curves