

**TECHSPEC® 76.2 x 178.5mm EFL 45° Protected Aluminum 100Å Off-Axis Parabolic Mirror**



Stock **#35-588** **2 In Stock**

[Other Coating Options](#)

1  £519<sup>20</sup>

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | £519.20 each                  |
| Qty 6-10       | £467.20 each                  |
| Qty 11+        | £448.00 each                  |
| Need More?     | <a href="#">Request Quote</a> |

**!** Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Off-Axis Parabolic Mirror **Type:**

**Physical & Mechanical Properties**

126.26 **Y Offset (mm):**

|   |   |
|---|---|
| 76.20 +0.00/-0.38   | <b>Diameter (mm):</b>                   |
| 90  | <b>Clear Aperture (%):</b>              |
| <100 RMS  | <b>Surface Roughness (□):</b>           |
| <b>Optical Properties</b>   |   |
| Metal   | <b>Coating Type:</b>                    |
| Protected Aluminum (400-2000nm)   | <b>Coating:</b>                         |
| 45  | <b>Off-Set Angle (°):</b>               |
| 400 - 2000  | <b>Wavelength Range (nm):</b>           |
| 178.53  | <b>Effective Focal Length EFL (mm):</b> |
| Aluminum 6061-T6  | <b>Substrate:</b> □                     |
| R <sub>avg</sub> ≥85% @400 - 700nm<br>R <sub>avg</sub> ≥97% @2,000 - 12,000nm | <b>Coating Specification:</b>           |
| ±1  | <b>Focal Length Tolerance (%):</b>      |
| 152.4   | <b>Parent Focal Length PFL (mm):</b>    |
| 3/4λ  | <b>Surface Figure, RMS:</b>             |
| 80-50   | <b>Surface Quality:</b>                 |
| 304.80  | <b>Radius of Curvature (mm):</b>        |
| 3/2λ  | <b>Reflected Wavefront, RMS:</b>        |

|                                 |                                    |
|---------------------------------|------------------------------------|
| <b>Threading &amp; Mounting</b> |                                    |
| #63-375                         | <b>Compatible Mounting Plates:</b> |

|                              |                                    |
|------------------------------|------------------------------------|
| <b>Regulatory Compliance</b> |                                    |
| Compliant                    | <b>RoHS 2015:</b>                  |
| View                         | <b>Certificate of Conformance:</b> |
| Compliant                    | <b>Reach 247:</b>                  |

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Aluminum Coatings for UV, Visible, and NIR Applications
- Range of Surface Roughness, Including 50Å and 100Å
- 15°, 30°, 45°, 60°, or 90° Offset Angle Options
- Gold and Silver Coated Off-Axis Parabolic Mirrors Also Available

TECHSPEC® Aluminum Off-Axis Parabolic Mirrors (OAPs) are a cost-effective solution for focusing incident light with minimal scatter loss. Available with enhanced or protected aluminum coatings, these OAP mirrors offer high reflectivity from the ultraviolet (UV) to the near infrared (NIR). These Aluminum OAPs are manufactured with multiple surface roughness specifications, offering designers the choice between high performance, low scatter mirrors and more cost sensitive options. TECHSPEC® Aluminum Off-Axis Parabolic Mirrors are used in optical systems such as Schlieren and spectroscopy systems, as well as in laser systems to focus laser beams. For increased system integration flexibility, mounting plates that thread to the base of these off-axis parabolic mirrors are available.

## Technical Information



;