

TECHSPEC[®] 76.2mm Dia. 515nm 0-45°, Yb:YAG Laser Line Mirror



TECHSPEC[®] Yb:YAG Laser Line Mirrors



Stock **#27-035** **2 In Stock**

-

1

+

£644^{.00}

ADD TO CART

Volume Pricing	
Qty 1-5	£644.00 each
Qty 6-25	£580.00 each
Qty 26-49	£516.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Laser Mirror		Type:
Physical & Mechanical Properties		
<3	Parallelism (arcmin):	
90	Clear Aperture (%):	
Commercial Polish		Back Surface:
76.20 +0.00/-0.10		Diameter (mm):
12.70 ±0.20		Thickness (mm):
Optical Properties		
10-5	Surface Quality:	
99.8	Reflection at DWL (%):	
R _{abs} >99.8% @ 515nm		Coating Specification:
509 - 520		Wavelength Range (nm):
λ/10		Surface Flatness (P-V):
Dielectric		Coating Type:
Laser Mirror (515nm)		Coating:
515		Design Wavelength DWL (nm):
0-45		Angle of Incidence (°):
Fused Silica (Corning 7980)		Substrate: □
10 J/cm² @ 515nm, 20ns, 20Hz		Damage Threshold, By Design: □
Regulatory Compliance		
Compliant		RoHS 2015:
View		Certificate of Conformance:
Compliant		Reach 250:

PRODUCT DETAILS

- >99.8% Reflectivity at Yb:YAG Harmonic Frequencies
 - Guaranteed High Laser Damage Thresholds
 - 10-5 Surface Quality for Reduced Scatter in Laser Applications
 - TECHSPEC® Laser Mirror Substrates and TECHSPEC® Nd:YAG Laser Line Mirrors Also Available
- TECHSPEC® Yb:YAG Laser Line Mirrors are designed to meet the demanding requirements of Ytterbium doped fiber (Yb:doped fiber) and thin-disk laser systems. These mirrors feature laser grade substrates with λ/10 surface flatness and 10-5 surface quality to minimize scattering effects. The durable dielectric coatings are designed for high reflectivity at their design wavelengths as well as high damage thresholds at both continuous wave and pulsed laser operating conditions. TECHSPEC Yb:YAG Laser Line Mirrors are ideal for laser applications that include laser ablation, welding, drilling, cutting, and sintering. Dielectric Yb:YAG mirror coatings for applications which require 343nm, 515nm, and 1030nm are available.
- Note:** Contact us for customizable wavelengths, sizes, and varying AOI versions.

CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).