

Fiber Optic Faceplate, 75 x 50 x 5mm



Fiber Optic Faceplates

Stock **#55-143** [CONTACT US](#)

-

1

+

£1,464⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	£1,464.00 each
Qty 5-24	£1,292.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

75 / 25

Core/ Clad Ratio:

Physical & Mechanical Properties

75 x 50 x 5

Dimensions (mm):

±0.1

Thickness Tolerance (mm):

Dimensional Tolerance (mm):	
±0.2	
Optical Properties	
1.00	Distortion (%):
	Substrate: ☐
Schott 47A Glass with EMA	
1.00	Numerical Aperture NA:
	Resolution:
102 lp/mm	
80-50	Surface Quality:
	Resolving Power (µm):
6.00	
Material Properties	
Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C):	
6.8	
Environmental & Durability Factors	
Operating Temperature (°C):	
-10 to +300	
Regulatory Compliance	
Certificate of Conformance:	
View	

Product Details

- Coherent Arrangement of Fibers
- Made with EMA Fibers to Absorb Light
- Round-to-Round or Round-to-Rectangular Tapers Types Available

Fiber Optic Tapers utilize a coherent fiber optic plate that transmits either a magnified or reduced image from its input surface to its output surface. These low distortion tapers are made with EMA Fibers to absorb light and are optimized for 1/2" or 2/3" sensor chip sizes. Magnification is a ratio of the diameters of the large and small ends of the tapers. Typical applications include image magnification or reduction, sensor coupling, fluoroscopy, and light sensors.

Fiber Optic Faceplates transmit images from input surface to output surface using coherent fibers. Common uses include CRT/LCD displays, sensor coupling, X-ray imaging and image intensification. All tapers and faceplates are suitable for visible and NIR applications and feature beveled edges.