


TECHSPEC[®] 25.4mm Dia. Uncoated, Silicon, Laser Mirror



Stock #90-139 NEW 1 In Stock

-

1

+

£78⁴⁰

ADD TO CART

Volume Pricing	
Qty 1+	£78.40 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:
Laser Mirror Substrate

Physical & Mechanical Properties

Parallelism (arcmin):
<3

Clear Aperture (%):
90

Back Surface:
Commercial Polish

25.40 +0.00/-0.10	Diameter (mm):
6.35 ±0.10	Thickness (mm):
Optical Properties	
40-20	Surface Quality:
N/A	Coating Specification:
λ/10	Surface Flatness (P-V):
Uncoated	Coating:
Optical Grade Silicon	Substrate: ☐
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Silicon Substrate for Thermally Demanding Ultrafast Setups
 - λ/10 Surface Flatness and 40-20 Surface Quality
 - Available In Standard Diameters for Coating Flexibility and System Integration
- TECHSPEC® Silicon Laser Mirror Substrates feature a high-thermal-conductivity silicon substrate designed for thermally demanding high-power and ultrafast laser applications. Optimized for efficient heat distribution in challenging optical setups, these substrates help mitigate thermally induced wavefront distortion. Designed as a coating-ready platform, TECHSPEC® Silicon Laser Mirror Substrates provide a flexible foundation for custom broadband or low-dispersion mirror solutions. Available in 12.7mm, 25.4mm, and 50.8mm diameters, these mirrors offer flexibility for integration into a wide range of laser system configurations.