

[See all 13 Products in Family](#)

75mm Dia., 0.7mm Thick, EAGLE XG® Window



EAGLE XG® Windows

Stock #29-369 **20+ In Stock**

⊖ 1 ⊕ £36²⁰

ADD TO CART

Volume Pricing	
Qty 1-5	£36.20 each
Qty 6-25	£28.80 each
Qty 26-49	£27.20 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:
Protective Window

Type of Window:
Glass

Physical & Mechanical Properties

Clear Aperture CA (mm):

67.50

Diameter (mm):

75.00 ±0.25

Thickness (mm):

0.70 ±0.07

Bevel:

Protective as needed

Clear Aperture (%):

90

Edges:

Ground and Seamed

Poisson's Ratio:

0.23

Young's Modulus (GPa):

73.6

Optical Properties

Coating:

Uncoated

Substrate:

EAGLE XG®

Index of Refraction (n_d):

1.51

Surface Quality:

80-50

Wavelength Range (nm):

350 - 2000

Material Properties

Density (g/cm^3):

2.38

Coefficient of Thermal Expansion CTE ($10^{-6}/^{\circ}C$):

3.17 (0 to +300°C)

Regulatory Compliance

RoHS 2015:

Compliant

Certificate of Conformance:

[View](#)

Reach 247:

Compliant

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Thin 0.7mm EAGLE XG® Substrates
- High Chemical Resistance and Excellent Durability
- Low Density for Weight Sensitive Applications

EAGLE XG® Windows are constructed from heavy-metal free glass through a fusion drawn process, providing these windows with exceptionally smooth, flat surfaces. These windows have high transmission in the visible spectrum, excellent environmental durability, and high chemical resistance. The low density of Corning® EAGLE XG® coupled with the thinness of these windows makes them ideal for weight and space sensitive applications. EAGLE XG® Windows are used as substrates for mobile device LCDs, substrates for polarizers, wafers for semiconductor applications, or protective windows for electronic displays.

Technical Information

EAGLE XG® Typical Transmission



Quote Your Size
