

830 Grooves/mm, 12.7mm Sq, UV Transmission Grating Beamsplitter



Stock #85-289 3-4 DAYS

-

1

+

£97.75

ADD TO CART

Qty 1-9
£97.75
Qty 10+
£87.97
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Groove Density (grooves/mm):
830

Wavelength Range (nm):
250 - 450

Blaze Angle (°):
19.4

Dimensions (mm): 12.70 x 12.70
Construction: Blazed Grating
Length (mm): 12.70
Substrate: ☐ Fused Silica (Corning 7980)
Thickness (mm): 2.00 ±0.5
Type: Transmission Diffraction Grating
Width (mm): 12.70
Alignment of Grooves to Edge (°): ±0.5

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View