

790nm CWL, 10nm FWHM, 12.5mm Mounted Diameter



Stock #67-779 3-4 DAYS

⊖ 1 ⊕ **£75.65**

ADD TO CART

Qty 1-9

£75.65

Qty 10+

£68.25

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.50 +0.00/-0.25

Angle of Incidence (°):
0

Optical Density OD (Average):
≥4.0

Clear Aperture CA (mm):

9.0

Center Wavelength CWL (nm):

790.00 +3.0/-1.0

Center Wavelength CWL Tolerance (nm):

+3.0/-1.0

Full Width-Half Max FWHM (nm):

10.00 ±2

Full Width-Half Max FWHM Tolerance (nm):

±2

Minimum Transmission (%):

>50

Operating Temperature (°C):

-50 to +70

Coating:

Traditional Coated

Surface Quality:

80-50

Thickness Tolerance (mm):

±0.1

Type:

Bandpass Filter

Typical Applications:

General Filtering

Blocking Wavelength Range (nm):

200 - Far IR

Construction:

Mounted in Black Anodized Ring

Mount Thickness (mm):

5.9 ±0.1

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

REACH 241:

[Compliant](#)