

TECHSPEC® 7X, 1064nm Vega® Nd:YAG Laser Line Beam Expander



7X, 1064nm DAFixed YAG Beam Expander, #35-113

Stock **#35-113** 3-4 DAYS

⊖ 1 ⊕ **£398.65**

ADD TO CART

Qty 1-9

£398.65

Qty 10+

£351.90

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):
0

Coating:
Laser V-Coat (1064nm)

Design Wavelength DWL (nm):
1064

Entrance Aperture (mm): 7.1
Exit Aperture (mm): 26
Expansion Power: 7X
Substrate: ☐ Fused Silica (Corning 7980)
Length (mm): 85.60
Mounting Threads: Input: Male M30 x 1 Output: Female M34 x 0.5 (not intended for use)
Transmission (%): >98.5 (nominal)
Type: Beam Expander
Weight (g): 171
Housing Diameter (mm): 39.95
Transmitted Wavefront, P-V: <λ/10 for 3.6mm input beam (nominal, λ = DWL)
Coating Specification: R _{abs} <0.25% @ 1064nm
Wavelength Range (nm): 1000 - 1140
Style: Fixed Magnification
Damage Threshold, By Design: ☐ 10 J/cm² @ 1064nm, 10ns, 20Hz
Divergence Adjustment: Rotating Optics

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View