


TECHSPEC® 9.53 x 6.35mm 1064nm 0-45°, Nd:YAG Laser Line Mirror



TECHSPEC® Nd:YAG Laser Line Mirrors

Stock **#39-658** CLEARANCE 3-4 DAYS

⊖ 1 ⊕ **£80.71**

ADD TO CART

Qty 1+

£80.71

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Quality:
10-5

Type:
Laser Mirror

Parallelism (arcmin):
<3

Clear Aperture (%):
85

Back Surface:

Commercial Polish
Reflection at DWL (%) : 99.8
Coating Specification : R _{abs} >99.8% @ 1064nm
Surface Flatness (P-V) : λ/10
Coating Type : Dielectric
Coating : Laser Mirror (1064nm)
Design Wavelength DWL (nm) : 1064
Dimensions (mm) : 9.53 x 6.35 +0.00/-0.10
Thickness (mm) : 3.18 ±0.20
Angle of Incidence (°) : 0-45
Substrate : ☐ Fused Silica (Corning 7980)
Damage Threshold, Reference : ☐ 15 J/cm² @ 1064nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015 : Compliant
Reach 209 : Compliant
Certificate of Conformance : View