

TECHSPEC[®] 9.0mm Diameter x -12 FL, NIR II Inked, Plano-Concave Lens



Stock **#67-988-INK** [CONTACT US](#)

[Other Coating Options](#)

-

1

+

£45⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-9	£45.60 each
Qty 10-25	£40.80 each
Qty 26-49	£36.60 each
Need More?	Request Quote

!

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Plano-Concave Lens

Type:

Physical & Mechanical Properties

9.00 ±0.025	Diameter (mm):
2.25	Center Thickness CT (mm):
±0.05	Center Thickness Tolerance (mm):
<1	Centering (arcmin):
8.10	Clear Aperture CA (mm):
3.24	Edge Thickness ET (mm):

Optical Properties

-12.00	Effective Focal Length EFL (mm):
N-SF11	Substrate:
1.33	f/#:
NIR II (750-1550nm)	Coating:
750 - 1550	Wavelength Range (nm):
-13.26	Back Focal Length BFL (mm):
R _{abs} ≤1.5% @ 750 - 800nm R _{abs} ≤1.0% @ 800 - 1550nm R _{avg} ≤0.7% @ 750 - 1550nm	Coating Specification:
587.6	Focal Length Specification Wavelength (nm):
±1.00	Focal Length Tolerance (%):
-9.42	Radius R ₁ (mm):
40-20	Surface Quality:
8 J/cm ² @ 1064nm, 10ns	Damage Threshold, By Design:
1.5λ	Power (P-V) @ 632.8nm:
λ/4	Irregularity (P-V) @ 632.8nm:

Regulatory Compliance

View	Certificate of Conformance:
------	-----------------------------

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- AR Coated to Provide <0.7% Reflectance per Surface for 750 - 1550nm
- Designed for 0° Angle of Incidence
- Various Coating Options: [Uncoated](#), [VIS-EXT](#), [MgF₂](#), [VIS 0°](#), [VIS-NIR](#), [YAG-BBAR](#), and [NIR I](#)

TECHSPEC® NIR II Coated Plano-Concave (PCV) Lenses are designed to bend parallel input rays to diverge from one another on the lens's output side causing this lens to have a negative focal length. These lenses can be used for balancing aberrations created by other lenses within a system due to their negative spherical aberration. Plano-Concave (PCV) lenses are commonly used in a variety of applications including image reduction, beam expansion and telescopes. TECHSPEC NIR II Coated Plano-Concave (PCV) Lenses offer optimal performance in the 750 to 1550nm range. These lenses are also available [Uncoated](#), [VIS-EXT](#), [MgF₂](#), [VIS 0°](#), [VIS-NIR](#), [YAG-BBAR](#), or with [NIR I](#) AR coating options.

Technical Information



N-BK7																									
Uncoated N-BK7 Typical Transmission <table border="1"><caption>Approximate data for Uncoated N-BK7 Typical Transmission</caption><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>200</td><td>70</td></tr><tr><td>400</td><td>92</td></tr><tr><td>600</td><td>93</td></tr><tr><td>800</td><td>93</td></tr><tr><td>1000</td><td>93</td></tr><tr><td>1200</td><td>93</td></tr><tr><td>1400</td><td>92</td></tr><tr><td>1600</td><td>93</td></tr><tr><td>1800</td><td>92</td></tr><tr><td>2000</td><td>91</td></tr><tr><td>2200</td><td>88</td></tr></tbody></table>	Wavelength (nm)	Transmission T (%)	200	70	400	92	600	93	800	93	1000	93	1200	93	1400	92	1600	93	1800	92	2000	91	2200	88	Typical transmission of a 3mm thick, uncoated N-BK7 window across the UV - NIR spectra. Click Here to Download Data
Wavelength (nm)	Transmission T (%)																								
200	70																								
400	92																								
600	93																								
800	93																								
1000	93																								
1200	93																								
1400	92																								
1600	93																								
1800	92																								
2000	91																								
2200	88																								
N-BK7 with MgF₂ Coating Typical Transmission <table border="1"><caption>Approximate data for N-BK7 with MgF₂ Coating Typical Transmission</caption><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>200</td><td>70</td></tr><tr><td>400</td><td>95</td></tr><tr><td>600</td><td>98</td></tr><tr><td>800</td><td>95</td></tr><tr><td>1000</td><td>94</td></tr><tr><td>1200</td><td>94</td></tr><tr><td>1400</td><td>93</td></tr><tr><td>1600</td><td>93</td></tr><tr><td>1800</td><td>93</td></tr><tr><td>2000</td><td>92</td></tr><tr><td>2200</td><td>90</td></tr></tbody></table>	Wavelength (nm)	Transmission T (%)	200	70	400	95	600	98	800	95	1000	94	1200	94	1400	93	1600	93	1800	93	2000	92	2200	90	Typical transmission of a 3mm thick N-BK7 window with MgF₂ (400-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 1.75\% @ 400 - 700\text{nm}$ (N-BK7) Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Wavelength (nm)	Transmission T (%)																								
200	70																								
400	95																								
600	98																								
800	95																								
1000	94																								
1200	94																								
1400	93																								
1600	93																								
1800	93																								
2000	92																								
2200	90																								
N-BK7 with VIS-EXT Coating Typical Transmission <table border="1"><caption>Approximate data for N-BK7 with VIS-EXT Coating Typical Transmission</caption><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>200</td><td>70</td></tr><tr><td>350</td><td>95</td></tr><tr><td>400</td><td>98</td></tr><tr><td>600</td><td>99</td></tr><tr><td>700</td><td>98</td></tr><tr><td>800</td><td>95</td></tr><tr><td>1000</td><td>85</td></tr><tr><td>1200</td><td>78</td></tr></tbody></table>	Wavelength (nm)	Transmission T (%)	200	70	350	95	400	98	600	99	700	98	800	95	1000	85	1200	78	Typical transmission of a 3mm thick N-BK7 window with VIS-EXT (350-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.5\% @ 350 - 700\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data						
Wavelength (nm)	Transmission T (%)																								
200	70																								
350	95																								
400	98																								
600	99																								
700	98																								
800	95																								
1000	85																								
1200	78																								
N-BK7 with VIS-NIR Coating Typical Transmission <table border="1"><caption>Approximate data for N-BK7 with VIS-NIR Coating Typical Transmission</caption><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>200</td><td>75</td></tr><tr><td>400</td><td>98</td></tr><tr><td>600</td><td>99</td></tr><tr><td>800</td><td>98</td></tr><tr><td>1000</td><td>95</td></tr><tr><td>1200</td><td>78</td></tr></tbody></table>	Wavelength (nm)	Transmission T (%)	200	75	400	98	600	99	800	98	1000	95	1200	78	Typical transmission of a 3mm thick N-BK7 window with VIS-NIR (400-1000nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 0.25\% @ 880\text{nm}$ $R_{avg} \leq 1.25\% @ 400 - 870\text{nm}$ $R_{avg} \leq 1.25\% @ 890 - 1000\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data										
Wavelength (nm)	Transmission T (%)																								
200	75																								
400	98																								
600	99																								
800	98																								
1000	95																								
1200	78																								

	
N-BK7 with VIS 0° Coating Typical Transmission 	Typical transmission of a 3mm thick N-BK7 window with VIS 0° (425-675nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.4\% @ 425 - 675\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
N-BK7 with YAG-BBAR Coating Typical Transmission 	Typical transmission of a 3mm thick N-BK7 window with YAG-BBAR (500-1100nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 0.25\% @ 532\text{nm}$ $R_{abs} \leq 0.25\% @ 1064\text{nm}$ $R_{avg} \leq 1.0\% @ 500 - 1100\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
N-BK7 with NIR I Coating Typical Transmission 	Typical transmission of a 3mm thick N-BK7 window with NIR I (600 - 1050nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.5\% @ 600 - 1050\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
N-BK7 with NIR II Coating Typical Transmission 	Typical transmission of a 3mm thick N-BK7 window with NIR II (750 - 1550nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 1.5\% @ 750 - 800\text{nm}$ $R_{abs} \leq 1.0\% @ 800 - 1550\text{nm}$ $R_{avg} \leq 0.7\% @ 750 - 1550\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data

Compatible Mounts

;