

TECHSPEC[®] 9.0mm Diameter x -18 FL, NIR I Coated, Plano-Concave Lens



Stock **#49-523** 20+ In Stock

☐ [Other Coating Options](#)

-

1

+

£36^{.00}

ADD TO CART

Volume Pricing	
Qty 1-9	£36.80 each
Qty 10-25	£33.00 each
Qty 26-49	£29.40 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Plano-Concave Lens

Type:

Physical & Mechanical Properties

9.00 +0.0/-0.025	Diameter (mm):
Protective as needed	Bevel:
2.25	Center Thickness CT (mm):
±0.05	Center Thickness Tolerance (mm):
<1	Centering (arcmin):
8.1	Clear Aperture CA (mm):
2.89	Edge Thickness ET (mm):
Optical Properties	
-18.00	Effective Focal Length EFL (mm):
N-SF11	Substrate: ☐
2.00	f/#:
0.25	Numerical Aperture NA:
NIR I (600-1050nm)	Coating:
600 - 1050	Wavelength Range (nm):
-19.26	Back Focal Length BFL (mm):
R _{avg} ≤0.5% @ 600 - 1050nm	Coating Specification:
587.6	Focal Length Specification Wavelength (nm):
±1	Focal Length Tolerance (%):
-14.12	Radius R ₁ (mm):
40-20	Surface Quality:
7 J/cm ² @ 1064nm, 10ns	Damage Threshold, By Design: ☐
1.5λ	Power (P-V) @ 632.8nm:
λ/4	Irregularity (P-V) @ 632.8nm:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume


Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details






- AR Coated to Provide <0.5% Reflectance per Surface for 600 - 1050nm
- Designed for 0° Angle of Incidence
- Various Coating Options: [Uncoated](#), [VIS-EXT](#), [MgF₂](#), [VIS 0°](#), [VIS-NIR](#), [YAG-BBAR](#), and [NIR II](#)

TECHSPEC® NIR I Coated Plano-Concave (PCV) Lenses are designed to bend parallel input rays to diverge from one another on the output side of the lens causing this lens to have a negative focal length. These lenses can be used for balancing aberrations created by other lenses within a system due to their negative spherical aberration. Plano-Concave (PCV) lenses are commonly used in a variety of applications including image reduction, beam

Technical Information



Uncoated N-BK7 Typical Transmission <table border="1"><caption>Approximate data for Uncoated N-BK7 Typical Transmission</caption><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>200</td><td>70</td></tr><tr><td>300</td><td>85</td></tr><tr><td>400</td><td>92</td></tr><tr><td>600</td><td>92</td></tr><tr><td>800</td><td>92</td></tr><tr><td>1000</td><td>92</td></tr><tr><td>1200</td><td>92</td></tr><tr><td>1400</td><td>92</td></tr><tr><td>1600</td><td>92</td></tr><tr><td>1800</td><td>92</td></tr><tr><td>2000</td><td>91</td></tr><tr><td>2200</td><td>89</td></tr></tbody></table>		Wavelength (nm)	Transmission T (%)	200	70	300	85	400	92	600	92	800	92	1000	92	1200	92	1400	92	1600	92	1800	92	2000	91	2200	89	Typical transmission of a 3mm thick, uncoated N-BK7 window across the UV - NIR spectra. Click Here to Download Data
Wavelength (nm)	Transmission T (%)																											
200	70																											
300	85																											
400	92																											
600	92																											
800	92																											
1000	92																											
1200	92																											
1400	92																											
1600	92																											
1800	92																											
2000	91																											
2200	89																											
N-BK7 with MgF₂ Coating Typical Transmission <table border="1"><caption>Approximate data for N-BK7 with MgF2 Coating Typical Transmission</caption><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>200</td><td>70</td></tr><tr><td>300</td><td>90</td></tr><tr><td>400</td><td>98</td></tr><tr><td>600</td><td>98</td></tr><tr><td>800</td><td>97</td></tr><tr><td>1000</td><td>96</td></tr><tr><td>1200</td><td>95</td></tr><tr><td>1400</td><td>94</td></tr><tr><td>1600</td><td>94</td></tr><tr><td>1800</td><td>93</td></tr><tr><td>2000</td><td>92</td></tr><tr><td>2200</td><td>90</td></tr></tbody></table>		Wavelength (nm)	Transmission T (%)	200	70	300	90	400	98	600	98	800	97	1000	96	1200	95	1400	94	1600	94	1800	93	2000	92	2200	90	Typical transmission of a 3mm thick N-BK7 window with MgF₂ (400-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 1.75\% @ 400 - 700\text{nm}$ (N-BK7) Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Wavelength (nm)	Transmission T (%)																											
200	70																											
300	90																											
400	98																											
600	98																											
800	97																											
1000	96																											
1200	95																											
1400	94																											
1600	94																											
1800	93																											
2000	92																											
2200	90																											
N-BK7 with VIS-EXT Coating Typical Transmission <table border="1"><caption>Approximate data for N-BK7 with VIS-EXT Coating Typical Transmission</caption><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>200</td><td>70</td></tr><tr><td>300</td><td>85</td></tr><tr><td>400</td><td>98</td></tr><tr><td>600</td><td>98</td></tr><tr><td>800</td><td>95</td></tr><tr><td>1000</td><td>85</td></tr><tr><td>1200</td><td>78</td></tr></tbody></table>		Wavelength (nm)	Transmission T (%)	200	70	300	85	400	98	600	98	800	95	1000	85	1200	78	Typical transmission of a 3mm thick N-BK7 window with VIS-EXT (350-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.5\% @ 350 - 700\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data										
Wavelength (nm)	Transmission T (%)																											
200	70																											
300	85																											
400	98																											
600	98																											
800	95																											
1000	85																											
1200	78																											
N-BK7 with VIS-NIR Coating Typical Transmission <table border="1"><caption>Approximate data for N-BK7 with VIS-NIR Coating Typical Transmission</caption><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>200</td><td>70</td></tr><tr><td>300</td><td>85</td></tr><tr><td>400</td><td>98</td></tr><tr><td>600</td><td>98</td></tr><tr><td>800</td><td>98</td></tr><tr><td>1000</td><td>98</td></tr><tr><td>1200</td><td>95</td></tr></tbody></table>		Wavelength (nm)	Transmission T (%)	200	70	300	85	400	98	600	98	800	98	1000	98	1200	95	Typical transmission of a 3mm thick N-BK7 window with VIS-NIR (400-1000nm) coating at 0° AOI.										
Wavelength (nm)	Transmission T (%)																											
200	70																											
300	85																											
400	98																											
600	98																											
800	98																											
1000	98																											
1200	95																											

	The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 0.25\% @ 880nm$ $R_{avg} \leq 1.25\% @ 400 - 870nm$ $R_{avg} \leq 1.25\% @ 890 - 1000nm$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
N-BK7 with VIS 0° Coating Typical Transmission 	Typical transmission of a 3mm thick N-BK7 window with VIS 0° (425-675nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.4\% @ 425 - 675nm$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
N-BK7 with YAG-BBAR Coating Typical Transmission 	Typical transmission of a 3mm thick N-BK7 window with YAG-BBAR (500-1100nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 0.25\% @ 532nm$ $R_{abs} \leq 0.25\% @ 1064nm$ $R_{avg} \leq 1.0\% @ 500 - 1100nm$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
N-BK7 with NIR I Coating Typical Transmission 	Typical transmission of a 3mm thick N-BK7 window with NIR I (600 - 1050nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.5\% @ 600 - 1050nm$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
N-BK7 with NIR II Coating Typical Transmission 	Typical transmission of a 3mm thick N-BK7 window with NIR II (750 - 1550nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 1.5\% @ 750 - 800nm$ $R_{abs} \leq 1.0\% @ 800 - 1550nm$ $R_{avg} \leq 0.7\% @ 750 - 1550nm$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data

200	400	600	800	1000	1200	1400	1600	1800	2000	
Wavelength (nm)										

Compatible Mounts

;