

940nm 50mW Pigtailed Laser Diode



Stock #23-795 [CONTACT US](#)

- 1 + £1,100⁷⁵

[ADD TO CART](#)

Volume Pricing	
Qty 1-9	£1,100.75 each
Qty 10+	£990.25 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Product Downloads



SPECIFICATIONS

General

Diode **Type of Laser:**

Laser Class - CDRH:

IIIb

Physical & Mechanical Properties

Length of Fiber (m):

1

Optical Properties

Numerical Aperture NA:

0.12

Spatial Mode:

Fiber-Coupled

Fiber Diameter (μm):

5

Wavelength (nm):

940.00 \pm 15

Color:

NIR

Electrical

Output Power (mW):

50

Hardware & Interface Connectivity

Operating Voltage (V):

5.0

Power Supply:

Power Supply Required and Sold Separately.

USA: [#73-818](#)

Europe: [#73-818](#)

Japan: [#13-640](#)

Korea: [#33-770](#)

China: [#73-818](#)

Connector:

FC/PC

Environmental & Durability Factors

Operating Temperature ($^{\circ}\text{C}$):

+15 to +30

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

Reach 233:

[Compliant](#)

PRODUCT DETAILS

- Single Mode Fiber with FC/PC Connector
- 1 to 100mW Output Power and 405 to 1550nm Wavelength Options
- Integrated Driver for Easy Operation

Pigtailed Laser Diode Modules feature an integrated 1m long, single mode fiber with an FC/PC connector. These laser diodes also feature an integrated driver for plug and play operation, only requiring a 5V external power supply ([#73-818](#)). Pigtailed Laser Diode Modules are available with VIS and NIR wavelengths ranging from 405 to 1550nm, with output powers ranging from 1 to 100mW. Their plug and play operation make these laser diodes ideal for a wide range of laboratory and OEM applications.