

Acrylic Filter 370nm 1mm thick, M30.5



Stock #71-931 **1 In Stock**

⊖ 1 ⊕ £45⁰⁰

ADD TO CART

Volume Pricing

Qty 1-9	£45.60 each
Qty 10+	£43.20 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Mounted Imaging Filter **Type:**

Physical & Mechanical Properties

25.50 **Clear Aperture CA (mm):**

32.50 **Outer Diameter (mm):**

Mounted in Black Anodized Ring

Construction:

1.00

Substrate Thickness (mm):

Optical Properties

370.00

Cut-On Wavelength (nm):

≥98

Minimum Transmission (%):

OLEO AR Coated Coating applied to both surfaces

Coating:

380 - 850

Transmission Wavelength (nm):

Threading & Mounting

M30.5 x 0.50

Filter Thread:

5.2

Mount Thickness (mm):

7.0

Mount Thickness Including Threads (mm):

Regulatory Compliance

Compliant

RoHS 2015:

View

Certificate of Conformance:

Compliant

Reach 242:

Product Details

- High Efficiency, Oleophobic Anti-Reflection Coating
- M22.5 through M105 Threaded Mount Options Available
- For Imaging Applications in the UV, VIS, and NIR Ranges

Acrylic Protective Longpass Filters cover the UV, VIS, and NIR spectral ranges and are designed with high-efficiency, anti-reflection oleophobic coatings that resist smudging, minimize light loss, and enhance performance. These filters offer a cost-effective way to protect expensive lenses and lighting from dirt, dust, liquids, impacts, and harsh conditions while maintaining image quality. Mounted in threaded mounts ranging from M22.5 to M105, these filters can be easily integrated into a variety of imaging applications. Acrylic Protective Longpass Filters achieve high transmission rates, typically exceeding 90% within their designed wavelength range. These filters are ideal for a diverse range of imaging applications such as industrial camera housings, dashboard cameras, LCD screen protection, and thermal uses as well as FDA and EFSA applications where the use of glass is not permitted and thickness is a concern.