

TECHSPEC® 9mm Dia., 0.41 Numerical Aperture, Uncoated, Precision Aspheric Lens



TECHSPEC® Precision Aspheric Lenses

Stock **#29-962** **13 In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ £295²⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-5 | £295.20 each |
| Qty 6-10 | £265.60 each |
| Qty 11-25 | £242.40 each |
| Need More? | Request Quote |

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Aspheric Lens **Type:**

Physical & Mechanical Properties

9.00 +0.00/-0.025 **Diameter (mm):**

| | |
|---------------------------|---|
| <3 | Centering (arcmin): |
| 6.75 | Clear Aperture CA (mm): |
| 2.56 | Edge Thickness ET (mm): |
| 4.00 ±0.10 | Center Thickness CT (mm): |
| Protective as needed | Bevel: |
| Plano | Shape of Back Surface: |
| Optical Properties | |
| 9.00 @587.6nm | Effective Focal Length EFL (mm): |
| 0.41 | Numerical Aperture NA: |
| 6.78 | Back Focal Length BFL (mm): |
| N-SF6 | Substrate: <input type="checkbox"/> |
| 587.6 | Aspheric Design Wavelength (nm): |
| 0.4λ | Asphere Figure Error, RMS @ 632.8nm: |
| Uncoated | Coating: |
| 40-20 | Surface Quality: |
| 1.20 | f#: |
| 390 - 2500 | Wavelength Range (nm): |
| Infinite | Conjugate Distance: |
| 111.11 | Power (diopters): |

| | |
|------------------------------|------------------------------------|
| Regulatory Compliance | |
| View | Certificate of Conformance: |

Product Details

- Improved Versions of Our Aspheric Lenses
 - Precision Grade Aspheric Surfaces
 - High Numerical Apertures to Maximize Throughput
- TECHSPEC® Precision Aspheric Lenses are CNC polished aspheric lenses that feature a 0.4λ RMS aspheric figure error. The precision aspheric figure error makes these lenses ideal for applications that require spherical aberration correction, including imaging and laser focusing applications. These aspheric lenses can also be used to replace multiple spherical elements in optical assemblies to reduce weight and cost. TECHSPEC Precision Aspheric Lenses are available with diameters from 6 to 50mm and high numerical apertures to maximize light throughput.