

TECHSPEC[®] 9mm Dia. x 40mm FL, VIS-NIR, Inked, Achromatic Lens



Stock #49-317-INK 3-4 DAYS
[Other Coating Options](#)

-

1

+

£73.10

ADD TO CART

Qty 1-5
£73.10
Qty 6+
£58.44
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
9.00 ±0.025

Effective Focal Length EFL (mm):

40.00
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 37.54
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 8.1
Centering (arcmin): <1
Center Thickness CT (mm): 5.06 ±0.10
Center Thickness CT 1 (mm): 3.73 ±0.05
Center Thickness CT 2 (mm): 1.33 ±0.05
Radius R ₁ (mm): 24.77
Radius R ₂ (mm): -18.01
Radius R ₃ (mm): -51.17
Edge Thickness ET (mm): 4.45
Substrate:  N-BK7 / N-SF5
Surface Quality: 40-20
f/#: 4.44
Numerical Aperture NA: 0.11
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @400 - 870nm R _{avg} ≤1.25% @890 - 1000nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 400 - 1000

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View