

**TECHSPEC® 9mm Inner Single Optic Mount**



TECHSPEC Multi-Element Inner Single Optic Mounts

Stock **#38-747** **6 In Stock**

⊖ 1 ⊕ £32.80

**ADD TO CART**

Volume Pricing	
Qty 1-4	£32.80 each
Qty 5+	£31.20 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Fixed **Type:**  
Optic Mount (Fixed) **Function:**

**Physical & Mechanical Properties**

**Construction:**  
Matte Black Anodized Aluminum (6061-T6)

9.0 Total Length (mm):

8.0 Clear Aperture CA (mm):

4.0 Max. Thickness of Compatible Optics (mm):

1.0 Min. Thickness of Compatible Optics (mm):

4.0 Edge Thickness of Compatible Optics (mm):

## Threading & Mounting

9.0 Diameter of Compatible Optics (mm):

M29 x 0.75 Thread Type:

## Regulatory Compliance

[Compliant](#) RoHS 2015:

[View](#) Certificate of Conformance:

[Compliant](#) Reach 250:

## Product Details

- Mounts for a Variety of Optical Component Diameters and Thicknesses
- M29 Outer Diameter Threads Allow Easy Positioning Within [Outer Tubes](#)
- One Retainer Ring and One Delrin Ring are Included
- Click [Here](#) to See How to Use the Multi-Element Tube System Components to Build an Optical System.

TECHSPEC® Multi-Element Inner Single Optic Mounts are designed to mount a variety of optical components. The mounts support optical diameters from 5mm to 25.4mm, and edge thicknesses of 4mm to 17mm. With M29 x 0.75 outer diameter threads, these mounts can be easily positioned along the optical axis of our TECHSPEC® Multi-Element Outer Tubes. TECHSPEC® Multi-Element Inner Single Optic Mounts include one Delrin ring to ensure secure clamping force between the retainer ring and optic without damaging the optic.

**Note:** Our specially designed ME Spanner Wrench ([#13-567](#)) is highly recommended to move Inner Single Optic Mounts back and forth smoothly utilizing a combined metric and English graduated scale. The hollow design enables transmission of output beam while adjusting lens position. Non-scaled ME Spanner Wrench ([#11-046](#)) is also available.