


[See all 3 Products in Family](#)

Basler ace2 a2A2840-14gmUV Ultraviolet (UV) GigE Camera

See More by [Basler](#)



Basler ace2 Ultraviolet (UV) GigE Camera



Stock **#72-580** **2 In Stock**

-

1

+

£5,376⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£5,376.00 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads	
UV	Spectrum:
General	
UV Camera	Type:
a2A2840-14gmUV	Model Number:

Basler	Manufacturer:
ace2	Camera Series:
Physical & Mechanical Properties	
36.3 x 29 x 29	Dimensions (mm):
<105	Weight (g):
Full	Housing:
Sensor	
Not Specified	Image Buffer:
2/3"	Sensor Format:
8.10	Resolution (Megapixels):
14.00	Frame Rate (fps):
2,856 x 2,848	Pixels (H x V):
2.74 x 2.74	Pixel Size, H x V (µm):
7.78 x 7.78	Sensing Area, H x V (mm):
Sony IMX487	Imaging Sensor:
Progressive Scan CMOS	Type of Sensor:
Global	Shutter Type:
8/10/12 Bit	Pixel Depth:
Freely Programmable	Exposure Time:
Not Specified	Dynamic Range (dB):
GigE Vision 2.0, GenICam	Machine Vision Standard:
Electrical	
3.2	Power Consumption (W):
Hardware & Interface Connectivity	
GigE (PoE)	Interface:
GigE, RJ45 with Screw Locks	Connector:
Power over Ethernet (PoE) or via GPIO with #16-644	Power Supply:
1 opto-coupled input line, 2 general purpose I/O (GPIO) lines	GPIOs:
Hardware Trigger (GPIO), Software Trigger, or Free-Run	Synchronization:
Back Panel	Interface Port Orientation:
6-pin M8	GPIO Connector Type:
Threading & Mounting	
C-Mount	Mount:
1/4-20 with Tripod Mount Adapter #16-641	Mounting Threads:
Environmental & Durability Factors	
-10 to 50	Operating Temperature (°C):
-20 to +80	Storage Temperature (°C):

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

Product Details

- UV (200 – 400nm) Imaging Capabilities with 8.1MP, 2.3" Sensor Format
- Compact Housing (29 x 29mm)
- Framerrates up to 67fps
- Powerful Computer VSION Feature Set with Beyond Features

Basler ace2 Ultraviolet (UV) Cameras integrate the Sony IMX487 Pregius S UV Sensor for high sensitivity in the 200 – 400nm UV spectrum. Featuring a compact 29 x 29mm form factor with 8.1MP sensor resolution, global shutter, and a 2/3" sensor format, these cameras are easily integrated into a variety of inspection applications. Basler ace2 Ultraviolet (UV) cameras integrate advanced Beyond software features for more efficient bandwidth use and more flexible scalability of pixel sizes, maximizing camera performance for demanding application requirements. These cameras are available in either GigE, 5GigE, or USB3.0 interfaces for high data throughput and are ideal for inspection applications operating within the ultraviolet (UV) wavelength such as wafer inspection, material sorting, security and surveillance, and solar inspection.