

[See all 127 Products in Family](#)

# Allied Vision Alvium 1800 U-040c, 1/2.9" 0.4MP S-Mount, Right Angle USB 3.1 Color Camera (Partial Housing)

See More by [Allied Vision](#)



Allied Vision Alvium Camera, Partial Housing, S-Mount, Right Angle IO Port (Front)

Stock **#14-856** [CONTACT US](#)

[Similar Cameras](#)

− 1 + £283<sup>.20</sup>

**ADD TO CART**

## Volume Pricing

Qty 1+	£283.20 each
Need More?	<a href="#">Request Quote</a>

Prices shown are exclusive of VAT/local taxes

## Product Downloads

Color **Spectrum:**

## General

Color Camera **Type:**

1800 U-040c **Model Number:**

Allied Vision  
Alvium Right Angle

**Manufacturer:**  
**Camera Series:**

## Physical & Mechanical Properties

25 x 32 x 29 (includes connectors and lens mount)  
45

**Dimensions (mm):**  
**Weight (g):**

Partial

**Housing:**

## Sensor

256KB  
1/2.9"

**Image Buffer:**  
**Sensor Format:**

0.40  
281.00

**Resolution (Megapixels):**  
**Frame Rate (fps):**

728 x 544  
6.9 x 6.9

**Pixels (H x V):**  
**Pixel Size, H x V (µm):**

5.0 x 3.8

**Sensing Area, H x V (mm):**

Sony IMX287  
Progressive Scan CMOS  
Global

**Imaging Sensor:**  
**Type of Sensor:**  
**Shutter Type:**

8/10/12 Bit  
177µs - 10s

**Pixel Depth:**  
**Exposure Time:**

Not Specified  
USB3 Vision v1.0, GenICam

**Dynamic Range (dB):**  
**Machine Vision Standard:**

## Electrical

1.9

**Power Consumption (W):**

## Hardware & Interface Connectivity

USB 3.1 Gen 1  
USB 3.1 Gen 1, Micro-B

**Interface:**  
**Connector:**

Power over USB or via GPIO  
4 Programmable TTL GPIOs

**Power Supply:**  
**GPIOs:**

Hardware Trigger (GPIO) or Software Trigger  
Back Panel (Right Angle)

**Synchronization:**  
**Interface Port Orientation:**

7-pin JST

**GPIO Connector Type:**

## Threading & Mounting

S-Mount (M12 x 0.5)  
1/4-20 and M6 with Tripod Mount Adapter [#14-156](#)

**Mount:**  
**Mounting Threads:**

## Environmental & Durability Factors

+5 to +65  
-10 to +70

**Operating Temperature (°C):**  
**Storage Temperature (°C):**

## Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 240:**

## Product Details

- Right Angle USB Port Orientation
- Compact, Low Cost, High Performance Design for Machine Vision and Embedded Applications
- ALMUM® System on Chip (SoC) Technology with Onboard Imaging Preprocessing
- [Allied Vision Alvium USB 3.1 Cameras](#) Also Available

Allied Vision Alvium Right Angle USB 3.1 Cameras feature ALMUM® System on Chip (SoC) technology and a right-angle USB port in a lightweight compact form factor, offering a comprehensive image processing library for advanced onboard image correction, preprocessing functions to relieve host computer and processor workload, and allow for easy system integration. In addition to smart camera operations, the unique SoC design also allows for low power consumption and ease of integration, making them ideal for next generation machine vision, robotics and embedded vision applications. The cameras feature a variety of popular Sony Pregius and On Semi CMOS sensors with high image quality, fast frame rate and USB3 Vision interface standard. The actively aligned lens mount minimizes inconsistency and variation. Allied Vision Alvium Right Angle USB 3.1 Cameras feature a 90° right angle USB port and are available in a variety of monochrome, color, and NIR configurations, including C-Mount, CS-Mount, and S-Mount. Full housing versions are best suited for prototyping, development and end user uses. Partial housing and board level configurations have exposed image sensor PCB without heat sinks to reduce space and facilitate system integration making them ideal for OEM embedded design.

**Note:** Board level versions do not have a lens mount.