

## BeamR2-Si Scanning Slit Beam Profiler



#24-215 DataRay Scanning Slit Beam Profiler

Stock **#24-215 1 In Stock**

⊖ 1 ⊕ £4,096<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	£4,096.00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### Physical & Mechanical Properties

60.96 x67.31 x66.17 **Dimensions (mm):**

±1µm **Dimensional Accuracy:**

### Optical Properties

190 - 1150 **Spectral Range:**

**Beam Diameter (µm):**

2µm to 4mm

## Sensor

5Hz **Frame Rate:**

## Electrical

1,000:1 **Signal to Noise S/N Ratio (dB):**

1 W Total & 0.5 mW/µm<sup>2</sup> **Maximum Power (W):**

## Threading & Mounting

1/4-20 thread **Mount:**

## Regulatory Compliance

[Exempt](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Contains SVHC\(s\)](#) **REACH 241:**

## Product Details

- Designed For Use From 190 to 1150nm
- Measure Beam Diameters of 2µm to 4mm
- Robust Easy to Use Software Provided

DataRay Scanning Slit Beam Profilers feature a silicon detector making it perfect for a 190 to 1150nm spectral range. Equipped with 2.5µm slits and larger knife-edge slits, the Beam'R2 is capable of measuring beams with diameters down to 2µm. Scanning slit instruments offer much higher resolution than camera-based systems, and are compatible with both continuous wave and pulsed laser sources. DataRay Scanning Slit Beam Profilers are ideal for optical assembly and instrument alignment, real-time diagnosis of focusing and alignment errors, real-time setting of multiple assemblies to the same focus. These profilers are USB 2.0 powered and include a 3m USB 2.0 cable.