

BWA-CAM Adapter Plate for 12MP Camera



Stock #86-903 NEW [CONTACT US](#)

-

1

+

£361²⁵

ADD TO CART

Volume Pricing	
Qty 1+	£361.25 each
Need More?	Request Quote

!

 Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

BWA-ADP-R6I12-EO

Model Number:

Physical & Mechanical Properties

81.0 x 78.0 x 12.4

Dimensions (mm):

Regulatory Compliance

[View](#)

Certificate of Conformance:

PRODUCT DETAILS

- Real-Time Analysis of Laser Beam Caustic, M², Centroid, Ellipticity, and Astigmatism
- Compatible with CW and Pulsed Lasers with Single-Pulse Capability
- Ideal for Laser Development, Quality Control, and Optical System Monitoring
- Complies with ISO 11146 and ISO 13694

Haas Laser Technologies BWA-CAMM² Analyzer Cameras offer real-time M² measurement for continuous wave and pulsed lasers in UV, VIS, or IR wavelength configurations. Featuring a simple “one-button” calibration, this system is capable of delivering M² measurements from a single pulse, making it ideal for dynamic or single-shot laser systems. Engineered in compliance with ISO 11146 and ISO 13694 standards, the BWA-CAM provides precise evaluation of critical spatial beam parameters, including M², beam profile, centroid, ellipticity, and astigmatism. Haas Laser Technologies BWA-CAMM² Analyzer Cameras enable users to detect optical system degradation early and optimize laser performance for maximum quality and process stability. The modular design of the BWA-CAM supports a broad range of laser wavelengths and application environments, while its high measurement accuracy and real-time data acquisition make it an essential tool for R&D, manufacturing, and laser system diagnostics.