

[See all 30 Products in Family](#)

C4020, 1.1" Color, DALSA Genie Nano GigE PoE Camera

See More by [Teledyne DALSA](#)



Teledyne DALSA Genie™ Nano GigE Cameras



Stock **#35-912** **5 In Stock**

[Similar Cameras](#)

-

1

+

£1,964⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£1,964.00 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

Color

Spectrum:

General

Color Camera

Type:

Model Number:

G3-GC11-C4020	
Teledyne DALSA	Manufacturer:
Genie Nano-1GigE	Camera Series:
Physical & Mechanical Properties	
40.6 x 29.0 x 44.0 (includes connectors and lens mount)	Dimensions (mm):
46	Weight (g):
Full	Housing:
Sensor	
200MB	Image Buffer:
1.1"	Sensor Format:
12.00	Resolution (Megapixels):
9.70	Frame Rate (fps):
20.00	Frame Rate - Burst Mode (fps):
4,112 x 3,012	Pixels (H x V):
3.45 x 3.45	Pixel Size, H x V (µm):
14.19 x 10.39	Sensing Area, H x V (mm):
Sony IMX304	Imaging Sensor:
Progressive Scan CMOS	Type of Sensor:
Global	Shutter Type:
8/12 bit	Pixel Depth:
Programmable or via external trigger	Exposure Time:
76.4	Dynamic Range (dB):
GigE Vision v1.2	Machine Vision Standard:
Electrical	
3.6 - 4.6 (12VDC External Power Supply) 4.0 - 4.9 (PoE)	Power Consumption (W):
Hardware & Interface Connectivity	
GigE (PoE)	Interface:
GigE, RJ45 with Screw Locks	Connector:
Power over Ethernet (PoE) or via GPIO	Power Supply:
2 digital input, 2 digital output	GPIOs:
Hardware Trigger (GPIO), Software Trigger, Free-Run, or PTP (IEEE 1588)	Synchronization:
Back Panel	Interface Port Orientation:
10-pin Samtec	GPIO Connector Type:
Threading & Mounting	
C-Mount	Mount:
1/4-20 with Tripod Mount Adapter #34-966	Mounting Threads:
Environmental & Durability Factors	

-20 to +60	Operating Temperature (°C):
-40 to +80	Storage Temperature (°C):

Regulatory Compliance	
Compliant	REACH 201:
View	Certificate of Conformance:

Product Details

- TurboDrive™ Technology Achieve Frame Rate up to 800 fps
- Compact, Lightweight, Robust All Metal Body
- Global Electronic Shutter with Exposure Control and Advanced Feature Set



Teledyne DALSA Genie™ Nano GigE Cameras are available in a range of Sony Pregius and On Semiconductor CMOS sensors. These GigE PoE cameras provide high speed, low noise, and global electronic shutters. The proprietary TurboDrive™ technology allows the Genie™ Nano to exceed standard frame rates, delivering up to 800 fps while retaining full image quality. These cameras come with a host of advanced feature set such as multi ROI windows and Burst Acquisition, which utilizes onboard memory buffer to achieve even faster frame rates.* Teledyne DALSA Genie™ Nano GigE Cameras are packaged in compact and robust all metal housing, making them ideal for electronics inspection, industrial metrology, and Intelligent Traffic Systems (ITS) applications.

Note: Frame rates achievable through TurboDrive™ or Burst Acquisition could vary with factors such as image quality and resolution.

Sapera LT is a free image acquisition and control software development toolkit (SDK) for Teledyne DALSA'S 1D cameras / 2D cameras / 3D Laser Profiler cameras and frame grabbers. Hardware independent in nature, Sapera LT offers a rich development ecosystem for machine vision OEMs and system integrators. Sapera LT supports image acquisition from cameras and frame grabbers based on machine vision standards including GigE Vision™, CameraLink®, CameraLink HS™, CoaXpress®, and USB3 Vision™.