

Cable GigE Cat 6 SFTP 5m

See More by [Teledyne DALSA](#)




Stock #68-470 **5 In Stock**

1 £8^{.00}

ADD TO CART

Cable GigE Cat 6 SFTP



Volume Pricing	
Qty 1+	£8.00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

- Drivers
- Spec Sheets
- User Manual:pdf

General

Type: Camera
Accessory

Regulatory Compliance

RoHS 2015: **Compliant**

Certificate of Conformance: [View](#)

Reach 235: **Compliant**

Product Details

- TurboDrive™ Technology Achieve Frame Rate up to 800 fps
- Compact, Lightweight, Robust All Metal Body
- Global Electronic Shutter with Exposure Control and Advanced Feature Set



Teledyne
Authorized
Distributor

Teledyne DALSA Genie™ Nano GigE Cameras are available in a range of Sony Pregius and On Semiconductor CMOS sensors. These GigE PoE cameras provide high speed, low noise, and global electronic shutters. The proprietary TurboDrive™ technology allows the Genie™ Nano to exceed standard frame rates, delivering up to 800 fps while retaining full image quality. These cameras come with a host of advanced feature set such as multi ROI windows and Burst Acquisition, which utilizes onboard memory buffer to achieve even faster frame rates.* Teledyne DALSA Genie™ Nano GigE Cameras are packaged in compact and robust all metal housing, making them ideal for electronics inspection, industrial metrology, and Intelligent Traffic Systems (ITS) applications.

Note: Frame rates achievable through TurboDrive™ or Burst Acquisition could vary with factors such as image quality and resolution.

Sapera LT is a free image acquisition and control software development toolkit (SDK) for Teledyne DALSA'S 1D cameras / 2D cameras / 3D Laser Profiler cameras and frame grabbers. Hardware independent in nature, Sapera LT offers a rich development ecosystem for machine vision OEMs and system integrators. Sapera LT supports image acquisition from cameras and frame grabbers based on machine vision standards including GigE Vision™, CameraLink®, CameraLink HS™, CoaXpress®, and USB3 Vision™.

Accessories

Note: Compatible accessories for individual stock numbers may vary. If unsure about which accessories work with your products, please contact us [here](#).

	Title	Compare	Stock Number	Price	Buy
MORE+	Cable GigE Cat 6 SFTP 5m		#68-470	£8.00 Request Quote	5 In Stock <input type="text" value="1"/>
MORE+	Power Over Ethernet (PoE) Single Port injector		#68-469	£53.00 Request Quote	2 In Stock <input type="text" value="1"/>
MORE+	Cable GigE Cat 6 SFTP 10m		#68-471	£14.00 Request Quote	4 In Stock <input type="text" value="1"/>
MORE+	Cable GigE Cat 6 SFTP 20m		#68-472	£23.00 Request Quote	1 In Stock <input type="text" value="1"/>
MORE+	Cable GigE Cat 6 SFTP 30m		#68-473	£31.00 Request Quote	1 In Stock <input type="text" value="1"/>
MORE+	Genie Nano GPIO 10-pin Cable, 2m		#16-032	£63.20 Request Quote	5 In Stock <input type="text" value="1"/>
MORE+	DALSA Genie Nano ¼-20 Mounting Adapter		#34-966	£42.40 Request Quote	6 In Stock <input type="text" value="1"/>
MORE+	DALSA Genie Nano Cable Kit		#34-967	£147.20 Request Quote	2 In Stock <input type="text" value="1"/>
MORE+	ACC-01-2101 4.5m CAT 5e Ethernet Cable		#70-312	£14.40 Request Quote	2 In Stock <input type="text" value="1"/>

Related Products



Teledyne DALSA Genie™ Nano GigE Cameras

Frequently Purchased Together



#03-627 - C-Mount Male to Olympus (RMS/DIN) Female Step-Down Adapter
£41.60



#03-629 - C-Mount Double Male Thread Ring
£29.40



#03-639 - 24" x 8", Breadboard
£238.40



#03-618 - 5mm Spacer to convert CS-Mount Cameras to C-Mount
£23.20

Resources

Media Type

- Application Note
- Video
- Published Article
- FAQ
- Glossary
- Technical Tool

APPLICATION NOTE

Sensor Performance and Limitations

APPLICATION NOTE

Imaging Electronics 101: Basics of Digital...

APPLICATION NOTE

Imaging Electronics 101: Camera Resolution for...

APPLICATION NOTE

Imaging Electronics 101: Understanding Camera...

VIDEO

How Do Cameras Work?

PUBLISHED ARTICLE

Advancements in Short Wave Infrared Sensors

[View More](#)