

[See all 15 Products in Family](#)

Coherent® EnergyMax 1110856 | 100nJ-200μJ, DB25

See More by [Coherent®](#)



Coherent® EnergyMax Laser Energy Sensors

Stock **#12-385** **5 In Stock**

-

1

+

£1,460⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£1,460.00 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
	Model Number:
J-10MT-10KHZ Coherent Part Number: 1110856	
	Type:
Meter required	
	Linearity (%):
±3	
	Calibration Uncertainty (%):
±2	

<10	Noise Equivalent Energy (μJ):
	Compatible Meters:
#35-203	

50mJ/cm ² (10ns, 1064nm)	Maximum Incident Energy Density:
	Energy Range:
100nJ - 200μJ	

#88-412	Preferred Meter:

Physical & Mechanical Properties

10	Active Area Diameter (mm):

Optical Properties

1064	Calibration Wavelength (nm):
	Maximum Pulse Width (μs):
1.7	

190 - 2100	Wavelength Range (nm):

Sensor

Pyroelectric	Type of Sensor:

Electrical

10000	Maximum Repetition Rate (pps):
	Maximum Incident Beam Power (W):
1	

Hardware & Interface Connectivity

DB25	Connector:
	Length of Cable (m):
2.5	

Regulatory Compliance

Exempt	RoHS 2015:
	Reach 224:
Contains SVHC(s)	

View	Certificate of Conformance:

Product Details

- ISO 17025 Certified
- Embedded Spectral Compensation Characteristics
- Automatic Temperature Compensation

Coherent® EnergyMax Laser Energy Sensors are designed for a variety of demanding laser measurement applications. These energy sensors, available in meter or meterless USB configurations, incorporate a diffuse coating to minimize specular reflection and feature large active areas. The J-50MB-YAG combines the MaxBlack coating with a diffuser for use with high energy lasers of up to 3J. Coherent® EnergyMax Laser Energy Sensors utilize onboard sensors to automate temperature compensation for improved measurement accuracy.