

Coherent® Thermopile Power Sensor 1098498 | 100mW - 30W, UV Coating, DB25

See More by [Coherent®](#)



Stock #12-406 [CONTACT US](#)

⊖ 1 ⊕ £1,196⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	£1,196.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Model Number:
PM30X
Coherent Part Number: 1098498

Type:
Meterless

Calibration Uncertainty (%):
±1

0.5 - 50 Long Pulse Joule Mode Range (J):

Air Cooling Method:

0.6 @ 1064nm, 10ns Maximum Incident Energy Density (J/cm²):

Physical & Mechanical Properties

19 Active Area Diameter (mm):

Optical Properties

10mW Resolution:

514 Calibration Wavelength (nm):

150 - 1000 Wavelength Range (nm):

0.15 - 1 Wavelength Range (μm):

Sensor

Thermopile Type of Sensor:

Electrical

50 (air-cooled) Maximum Intermittent Power, <5min (W):

6 Maximum Incident Power Density (kW/cm²):

100mW - 30W Power Range:

Hardware & Interface Connectivity

2.0 Length of Cable (m):

DB25 Computer Interface:

Regulatory Compliance

[Exempt](#) RoHS 2015:

[Contains SVHC\(s\)](#) Reach 224:

[View](#) Certificate of Conformance:

Product Details

- Superior Damage Resistance
- Wide Dynamic Range
- ISO 17025 Certified

Coherent® Thermopile Power Sensors are ideal for measuring the average power of continuous wave lasers or pulsed laser energy. Thermopile sensors operate by absorbing and converting incident laser radiation into heat, which then flows to a heat sink. The temperature difference between the absorber and heat sink is converted into an electrical signal by a thermocouple junction. Coherent® Thermopile Power Sensors, unlike semiconductor sensors, do not saturate. Unlike semiconductor sensors, thermopile sensors feature high power capability and flat spectral response.