

Dual Axis Linear Scale Micrometer on Opal Glass



Stock **#58-763** [CONTACT US](#)

-

1

+

£595^{.34}

ADD TO CART

Volume Pricing	
Qty 1-4	£595.34 each
Qty 5+	£565.75 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

No

NIST Certification:

Physical & Mechanical Properties

Metric: 25µm English: 1 mil (0.001")	Scale Divisions:
25.4 x 76.2	Dimensions (mm):
1.50 ±0.100	Thickness (mm):
±0.100	Dimensional Tolerance (mm):
Optical Properties	
Chrome on Opal Glass	Substrate:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

PRODUCT DETAILS

- Dual Axis Design
- English and Metric Scales
- NIST Certified Version Available

Our Linear Scale Stage Micrometer is designed to accurately calibrate machine vision systems simultaneously in the X- and Y- axes. This allows calibration without rotation, and without compensation for camera aspect ratios. Micrometer features two scales – a metric scale featuring 25µm divisions, and an English scale featuring 1 mil (0.001") divisions. Target is chrome on glass or chrome on opal.

TECHNICAL INFORMATION

